



- ErP¹, CEC² and EISA³ Compliant Models
- Wide Range AC Input
- Medical Certifications

Key Market Segments & Applications

Medical, Industrial Computing,
Life Sciences / Laboratory

DTM110-C Series

90W to 110W Medical AC-DC External Power Supplies

DTM110-C Features and Benefits

Features

- CEC and EISA Compliant
- Wide Range AC Input
- 87% Average Efficiency

Benefits

- Easier system compliance
- Global Operation
- Consumes less energy

Specifications


ITEMS		MODELS	DTM110PWxxx-C
Input Voltage range	VAC		90 - 264VAC (47 - 63Hz)
Inrush Current	A		100A at 230VAC input, 25°C ambient cold start
Input Current	A		2A at 90VAC, Full Load
Power Factor	-		Meets EN61000-3-2. >0.9 PF
Leakage Current (264VAC 60Hz)	μA		Typically 300μA
Hold Up Time (Typ)	ms		>10ms
Temperature Coefficient	%/°C		±0.05%/°C
Voltage Accuracy	%		±1%
Adjustment Range	V		None
Minimum Load	A		None
Total Regulation	%		12V to 15V Models: ±5%, >15V models ±3%
Ripple & Noise	%		1%
Short Circuit Protection	-		<160% - hiccup mode
Overvoltage Protection	V		110 - 150% of nominal (Cycle input power to reset)
Average Efficiency	%		87%
Operating Temperature	°C		0 to +40°C
Storage Temperature	°C		-10 to +70°C
Humidity (non condensing)	%RH		10 - 90%RH
Cooling	-		Convection
Withstand Voltage	VAC		Input to Ground 1.5kVAC, Input to Output 4kVAC
Vibration (non operating)	-		23.52m/s ² (10 - 55Hz: constant sweep 1 min X, Y, Z for 1 hour)
Shock	-		< 196.1 m/s ² (20G)
Safety Agency Approvals	-		CE, UL60601-1, EN60601-1, IEC60601-1
Safety Class	-		Class I
Altitude	m		3000m
Offload Power Consumption	W		< 0.5W
Conducted & Radiated EMI	-		EN60601-1-2, FCC Part 18 Class B
Immunity	-		EN55011
Weight (Typ)	g		605g
Size (WxLxH)	mm		170 x 64.8 x 38.5
Cable Length	mm		1050mm
AC Input Connector	-		IEC 320-C14 (Accepts IEC 320-C13)
Output Connector	-		Kycon KPPx-4P or equivalent Pins 1 & 2: -Vout, Pins 3 & 4: +Vout
Warranty	yrs		3

Notes: (1) ErP - Energy Related Products (2) Californian Energy Commission (3) EISA - Energy Independence and Security Act of 2007

Model Selector


Model	Output (V)	Maximum Output (A)	Maximum Power (W)	ErP	CEC	EISA Efficiency Level
DTM110PW120C	12	7.5	90	Step 2	V	V
DTM110PW135C	13.5	6.67	90	Step 2	V	V
DTM110PW150C	15	6.67	100	Step 2	V	V
DTM110PW190C	19	5.8	110	Step 2	V	V
DTM110PW200C	20	5.5	110	Step 2	V	V
DTM110PW240C	24	4.6	110	Step 2	V	V

Outline Drawing DTM110-C Series



Other External AC-DC Products - **DTM65-C, DTM65-C8, DTM165**

DTM110-C Output Connector



Pinout DTM110-C Model

Pin	Function
1	- Vout
2	- Vout
3	+ Vout
4	+ Vout

Alternative output connectors are available
Please contact Sales for further information (min quantities apply)



TDK-Lambda France SAS

3 Avenue du Canada
Parc Technopolis
Bâtiment Sigma
91940 les Ulis
France
Tel: +33 1 60 12 71 65
Fax: +33 1 60 12 71 66
france@fr.tdk-lambda.com
www.emea.lambda.tdk.com/fr



Italy Sales Office

Via Giacomo Matteotti 62
20092 Cinisello Balsamo (MI)
Italy
Tel: +39 02 61 29 38 63
Fax: +39 02 61 29 09 00
info.italia@it.tdk-lambda.com
www.emea.lambda.tdk.com/it



Netherlands

info@nl.tdk-lambda.com
www.emea.lambda.tdk.com/nl



TDK-Lambda Germany GmbH

Karl-Bold-Strasse 40
77855 Achern
Germany
Tel: +49 7841 666 0
Fax: +49 7841 5000
info.germany@de.tdk-lambda.com
www.emea.lambda.tdk.com/de



Austria Sales Office

Aredstrasse 22
2544 Leobersdorf
Austria
Tel: +43 2256 655 84
Fax: +43 2256 645 12
info@at.tdk-lambda.com
www.emea.lambda.tdk.com/at



Switzerland Sales Office

Eichtalstrasse 55
8634 Hombrechtikon
Switzerland
Tel: +41 44 850 53 53
Fax: +41 44 850 53 50
info@ch.tdk-lambda.com
www.emea.lambda.tdk.com/ch



Nordic Sales Office

Haderslevvej 36B
DK-6000 Kolding
Denmark
Tel: +45 8853 8086
info@dk.tdk-lambda.com
www.emea.lambda.tdk.com/dk



TDK-Lambda UK Ltd.

Kingsley Avenue
Ilfracombe
Devon EX34 8ES
United Kingdom
Tel: +44 (0) 12 71 85 66 66
Fax: +44 (0) 12 71 86 48 94
info@uk.tdk-lambda.com
www.emea.lambda.tdk.com/uk



TDK-Lambda Ltd.

1 Alexander Yanai
Segula
Petah-Tikva
Israel
Tel: +9 723 902 4333
Fax: +9 723 902 4777
info@tdk-lambda.co.il
www.emea.lambda.tdk.com/il



C.I.S.

Commercial Support:

Tel: +7 (495) 665 2627

Technical Support:

Tel: +7 (812) 658 0463
info@tdk-lambda.ru
www.emea.lambda.tdk.com/ru

Local Distribution