


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H2	ECR-22-141078	01JUN2022	RK	TB



NOTES:

- 100% OPEN SHORT AND MISPLACEMENT TEST.
HI-POT:300VDC/10MS
INSULATION:50MΩMIN.
CONDUCTOR RESISTANCE:1.0ΩMAX.
- NOTE FOR PACKAGING:
PACKING 50PCS IN ONE CARTON BOX.
LABEL PRINT FOLLOW THE PACKAGING SPECIFICATION 107-19759.
- PRINT ON CABLE AS BELOW (MARKING SIZE LEGIBLE, CUSTOMER PN ONLY IF AVAILBLE)

XXXXXXXXXTYYWW

CUSTOMER PN DATE CODE: YY:YEAR WW WEEK
VENDER CODE:T
- ALTERNATIVE PN 2265133-1.
- ALTERNATIVE PN 1760286-7.
- FOR OV STARZ ONLY:
USE SD829 EPOXY RESIN AB GLUE
FROM HUIZHOU SANDAO CO LTD
FOR THE MOLDING PROCESS

WIRING DIAGRAM		
FROM	COLOR	TO
P1-1	BROWN	P2
P1-2	YELLOW/GREEN	P4
P1-3	BLUE	P3

1-2142947-3	98460259	4000±100
1-2142947-2	98460258	1000±30
1-2142947-1	98373384	2000±30
2142947-4		720±20
2142947-3		4000±100
2142947-2		1000±30
2142947-1		2000±30
TE P/N	CUSTOMER P/N	L

3	3	3	-	-	-	PC	SPLICE TERMINAL 0.5-1.0MM ²	9
1	1	1	1	1	1	PC	LABEL 25*50MM WHITE25*13MM	8
-	-	-	3	3	3	PC	TUBULAR END SLEEVE 20AWG	7
AR	AR	AR	AR	AR	AR	KG	MOLD TPU, COLOR: BLACK ,DESMOPAN 786E	6
AR	AR	AR	AR	AR	AR	KG	INNER MOLD, PE, COLOR: CLEAR.	5
3	3	3	3	3	3	PC	TERMINAL, FOR 0.35-0.5MM ² , INSULATION OD: 1.4~1.7MM.	4
3	3	3	3	3	3	PC	SINGLE WIRE SEAL, COLOR: YELLOW.	3
1	1	1	1	1	1	PC	PLUG, 3POS, 1.5 SERIES CONNECTOR	2
AR	AR	AR	AR	AR	AR	MR	3X0.5MM ² . 90°C BLACK	1
1-3	1-2	1-1	-3	-2	-1	U/M	DESCRIPTION	ITEM

PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY ENVIRONMENTAL STANDARD TEC-138-702

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Tyron Peng 27MAR2013	TE Connectivity Ltd.		
		CHK Henry Hu 27MAR2013			
DIMENSIONS: mm		APVD Zandvoort van, Alex 27MAR2013	NAME Cable assy cable cpl. power UPM3 -		
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		APPLICATION SPEC	SIZE A3		
MATERIAL		WEIGHT	CAGE CODE 00779	DRAWING NO C-2142947	RESTRICTED TO
		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
				REV H2	