


D2F

Ultra Subminiature Basic Switch


Ultra Subminiature Basic Switch with plenty of terminal variations

- Incorporating a snapping mechanism made with two highly precise split springs that ensures long durability.
- Using insertion molded terminals that prevents flux penetration.
- In addition to self-clinching PCB, left-angled, right-angled terminals, 2 types of soldering terminals are available.
- Lineup of 5A type for high load applications.



D
2
F

Model Number Legend




List of Models

Actuator		Ratings Maximum Operating Force (OF) * Terminals	3 A	1 A	0.1 A		5 A
			General Purpose 1.47 N {150 gf}	Low Operating Force 0.74 N {75 gf}	General Purpose 1.47 N {150 gf}	Low Operating Force 0.74 N {75 gf}	General Purpose 1.47 N {150 gf}
	Pin plunger	PCB terminals (Standard)	D2F	D2F-F	D2F-01	D2F-01F	D2F-5
		Self-clinching PCB terminals	D2F-T	D2F-F-T	D2F-01-T	D2F-01F-T	-
		PCB terminals (Right-angled)	D2F-A	D2F-F-A	D2F-01-A	D2F-01F-A	
		PCB terminals (Left-angled)	D2F-A1	D2F-F-A1	D2F-01-A1	D2F-01F-A1	
		Solder terminals	D2F-D3	D2F-F-D3	D2F-01-D3	D2F-01F-D3	
		Compact solder terminals	D2F-D	D2F-F-D	D2F-01-D	D2F-01F-D	
	Hinge lever	PCB terminals (Standard)	D2F-L	D2F-FL	D2F-01L	D2F-01FL	D2F-5L
		Self-clinching PCB terminals	D2F-L-T	D2F-FL-T	D2F-01L-T	D2F-01FL-T	-
		PCB terminals (Right-angled)	D2F-L-A	D2F-FL-A	D2F-01L-A	D2F-01FL-A	
		PCB terminals (Left-angled)	D2F-L-A1	D2F-FL-A1	D2F-01L-A1	D2F-01FL-A1	
		Solder terminals	D2F-L-D3	D2F-FL-D3	D2F-01L-D3	D2F-01FL-D3	
		Compact solder terminals	D2F-L-D	D2F-FL-D	D2F-01L-D	D2F-01FL-D	
	Hinge roller lever	PCB terminals (Standard)	D2F-L2	D2F-FL2	D2F-01L2	D2F-01FL2	-
		Self-clinching PCB terminals	D2F-L2-T	D2F-FL2-T	D2F-01L2-T	D2F-01FL2-T	
		PCB terminals (Right-angled)	D2F-L2-A	D2F-FL2-A	D2F-01L2-A	D2F-01FL2-A	
		PCB terminals (Left-angled)	D2F-L2-A1	D2F-FL2-A1	D2F-01L2-A1	D2F-01FL2-A1	
		Solder terminals	D2F-L2-D3	D2F-FL2-D3	D2F-01L2-D3	D2F-01FL2-D3	
		Compact solder terminals	D2F-L2-D	D2F-FL2-D	D2F-01L2-D	D2F-01FL2-D	
	Simulated roller lever (R1.3)	PCB terminals (Standard)	D2F-L3	D2F-FL3	D2F-01L3	D2F-01FL3	D2F-5L3
		Self-clinching PCB terminals	D2F-L3-T	D2F-FL3-T	D2F-01L3-T	D2F-01FL3-T	-
		PCB terminals (Right-angled)	D2F-L3-A	D2F-FL3-A	D2F-01L3-A	D2F-01FL3-A	
		PCB terminals (Left-angled)	D2F-L3-A1	D2F-FL3-A1	D2F-01L3-A1	D2F-01FL3-A1	
		Solder terminals	D2F-L3-D3	D2F-FL3-D3	D2F-01L3-D3	D2F-01FL3-D3	
		Compact solder terminals	D2F-L3-D	D2F-FL3-D	D2F-01L3-D	D2F-01FL3-D	
	Simulated roller lever (R2.5)	PCB terminals (Standard)	D2F-L30	D2F-FL30	D2F-01L30	D2F-01FL30	-
		Self-clinching PCB terminals	D2F-L30-T	D2F-FL30-T	D2F-01L30-T	D2F-01FL30-T	
		PCB terminals (Right-angled)	D2F-L30-A	D2F-FL30-A	D2F-01L30-A	D2F-01FL30-A	
		PCB terminals (Left-angled)	D2F-L30-A1	D2F-FL30-A1	D2F-01L30-A1	D2F-01FL30-A1	
		Solder terminals	D2F-L30-D3	D2F-FL30-D3	D2F-01L30-D3	D2F-01FL30-D3	
		Compact solder terminals	D2F-L30-D	D2F-FL30-D	D2F-01L30-D	D2F-01FL30-D	

* OF are value for Pin plunger.

Contact Form

●SPDT



Contact Specifications

Item		Model	D2F models D2F-5 models	D2F-01 models
Contact	Specifications		Crossbar	
	Material		Silver alloy	Gold alloy
	Gap (standard value)		0.25 mm	
Minimum applicable load (see note) *			100 mA at 5 VDC	1 mA at 5 VDC

* Please refer to "Using Micro Loads" in "Precautions" for more information on the minimum applicable load.

Ratings

Model Maximum Operating Force (OF)	D2F models		D2F-01 models		D2F-5 models
	1.47N (General-purpose)	0.74N (Low Operating Force)	1.47N (General-purpose)	0.74N (Low Operating Force)	1.47N (General-purpose)
Rated voltage	Resistive load				
125 VAC	3 A	1 A	-		-
30 VDC	2 A	0.5 A	0.1 A		-
250 VAC	-		-		5 A

Note. The above rating values apply under the following test conditions.
(1) Ambient temperature: 20±2°C
(2) Ambient humidity: 65±5%
(3) Operating frequency: 30 operations/min

Approved Safety Standard

The items shown in the "List of Models" above are not standard approved models.
Consult your OMRON sales representative for specific models with standard approvals.
UL (UL61058-1)/cUL (CSA C22.2 No.61058-1)

Rated voltage	Model	D2F (General-purpose)	D2F (Low operating force)	D2F-01
30 VDC		2 A	0.5 A	0.1 A

Characteristics

Item		Model	D2F-01 models	D2F models		D2F-5 models
				0.74 N (Low operating force)	1.47 N (General-purpose)	1.47 N (General-purpose)
Permissible operating speed			Pin plunger models: 1 mm to 500 mm/s, Lever models: 5 mm to 500 mm/s			
Permissible operating frequency	Mechanical		Pin plunger models: 200 operations/min, Lever models: 100 operations/min			
	Electrical		30 operations/min			
Insulation resistance			100 MΩ min. (at 500 VDC with insulation tester)			
Contact resistance (initial value)			100 mΩ max.	50 mΩ max.	30 mΩ max.	
Dielectric strength	Between terminals of the same polarity		600 VAC 50/60 Hz for 1min			
	Between current-carrying metal parts and ground		1,500 VAC 50/60 Hz for 1min			
	Between each terminal and non-current-carrying metal parts		1,500 VAC 50/60 Hz for 1min			
Vibration resistance * 1	Malfunction		10 to 55 Hz, 1.5-mm double amplitude			
Shock resistance	Durability		1,000 m/s ² {approx. 100G} max.			
	Malfunction * 1		300 m/s ² {approx. 30G} max.			
Durability * 2	Mechanical		1,000,000 operations min. (60 operations/min)			
	Electrical		100,000 operations min. (30 operations/min)	30,000 operations min. (30 operations/min)		10,000 operations min. (30 operations/min)
Degree of protection			IEC IP40			
Ambient operating temperature			-40°C to +85°C (at ambient humidity 60% max.) (with no icing or condensation)			
Ambient operating humidity			85% max. (for +5°C to +35°C)			
Weight			Approx. 0.5 g (pin plunger models)			


Note. The data given above are initial values.

*1. The values are at Free Position and Total Travel Position values for pin plunger, and Total Travel Position value for lever.
Close or open circuit of the contact is 1ms max.


*2. For testing conditions, consult your OMRON sales representative.

Terminals/Apearances (Unit: mm)


●PCB terminals (Straight)




●Self-clinching PCB terminals




<PCB Mounting Dimensions (Reference)>




●PCB terminals (Right-angled)




●PCB terminals (Left-angled)




●Solder terminals



●Compact solder terminals



Mounting Holes (Unit: mm)



Dimensions (Unit: mm) /Operating Characteristics

The following illustrations and drawings are for D2F models with PCB terminals (straight). Self-clinching, solder, compact solder, and right-angled, left angled terminals are omitted from the following drawings. Refer to the **previous page** for these terminals.

When ordering, replace □ with the code for the terminal that you need. See the **"List of Models"** for available combinations of models.

●Pin Plunger Models



D2F-□

D2F-01□

D2F-F□

D2F-01F□

D2F-5



Operating Characteristics	Model	D2F-□ D2F-01□ D2F-5	D2F-F□ D2F-01F□
		Operating Force OF Max. 1.47 N {150 gf}	0.74 N {75 gf}
Releasing Force RF Min.		0.20 N {20 gf}	0.05 N {5 gf}
Pretravel PT Max.		0.5 mm	0.5 mm
Overtravel OT Min.		0.25 mm	0.25 mm
Movement Differential MD Max.		0.12 mm	0.12 mm
Operating Position OP		5.5±0.3 mm	

●Hinge Lever Models



D2F-L□

D2F-01L□

D2F-FL□

D2F-01FL□

D2F-5L



Operating Characteristics	Model	D2F-L□ D2F-01L□ D2F-5L	D2F-FL□ D2F-01FL□
		Operating Force OF Max. 0.78 N {80 gf}	0.25 N {25 gf}
Releasing Force RF Min.		0.05 N {5 gf}	0.02 N {2 gf}
Overtravel OT Min.		0.55 mm	0.55 mm
Movement Differential MD Max.		0.5 mm	0.5 mm
Free Position FP Max.		10 mm	
Operating Position OP		6.8±1.5 mm	

●Simulated Roller Lever Models (R1.3)



D2F-L3□

D2F-01L3□

D2F-FL3□

D2F-01FL3□

D2F-5L3



Operating Characteristics	Model	D2F-L3□ D2F-01L3□ D2F-5L3	D2F-FL3□ D2F-01FL3□
		Operating Force OF Max. 0.78 N {80 gf}	0.39 N {40 gf}
Releasing Force RF Min.		0.05 N {5 gf}	0.02 N {2 gf}
Overtravel OT Min.		0.5 mm	0.5 mm
Movement Differential MD Max.		0.45 mm	0.45 mm
Free Position FP Max.		13 mm	
Operating Position OP		8.5±1.2 mm	



●Simulated Roller Lever Models (R2.5)

D2F-L30□

D2F-01L30□

D2F-FL30□

D2F-01FL30□





Operating Characteristics	Model	D2F-L30□ D2F-01L30□	D2F-FL30□ D2F-01FL30□
		Operating Force OF Max. 0.54 N {55 gf}	0.3 N {31 gf}
Releasing Force RF Min.		0.04 N {4 gf}	0.02 N {2 gf}
Overtravel OT Min.		0.5 mm	0.5 mm
Movement Differential MD Max.		0.5 mm	0.5 mm
Free Position FP Max.		12.6 mm	
Operating Position OP		9.5±1.0 mm	

Note 1. Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

Note 2. The operating characteristics are for operation in the A direction (↓).

●Hinge Roller Lever Models

- D2F-L2□
- D2F-01L2□
- D2F-FL2□
- D2F-01FL2□



*1. Stainless-steel lever
*2. Polyacetal resin roller

Operating Characteristics	Model	D2F-L2□ D2F-01L2□	D2F-FL2□ D2F-01FL2□
Operating Force	OF Max.	0.78 N {80 gf}	0.39 N {40 gf}
Releasing Force	RF Min.	0.05 N {5 gf}	0.02 N {2 gf}
Overtravel	OT Min.	0.55 mm	0.55 mm
Movement Differential	MD Max.	0.5 mm	0.5 mm
Free Position	FP Max.	16.5 mm	
Operating Position	OP	13±2 mm	

Note 1. Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.
Note 2. The operating characteristics are for operation in the A direction (↓).

Precautions

★Please refer to "Basic Switches Common Precautions" for correct use.

Cautions

●Soldering

- Terminal connection
When soldering, make sure that the temperature of the soldering iron tip is not higher than 300°C, and complete the soldering within 3 seconds. Do not apply any external force for 1 minute after soldering. Soldering at an excessively high temperature or soldering for more than 3 seconds may deteriorate the characteristics of the Switch.
- Connecting to PCB terminal Boards
When using automatic soldering baths, we recommend soldering at 260°C ±5°C within 5 seconds. Make sure that the liquid surface of the solder does not flow over the edge of the board.
When soldering terminals manually, perform soldering within 3 seconds at iron tip temperature not higher than 350°C. Do not apply any external force for at least 1 minute after soldering.
When applying solder, keep the solder away from the case of the Switch and do not allow solder or flux to flow into the case.

Correct Use


●Mounting

Use M2 mounting screws with plane washers or spring washers to securely mount the Switch. Tighten the screws to a torque of 0.08 to 0.1 N·m {0.8 to 1 kgf·cm}.

●Using Micro Loads

Using a model for ordinary loads to open or close the contact of a micro load circuit may result in faulty contact. Use models that operate in the following range. However, even when using micro load models within the following operating range, if inrush current occurs when the contact is opened or closed, it may increase the contact wear and so decrease durability. Therefore, insert a contact protection circuit where necessary. The minimum applicable load is the N-level reference value. This value indicates the malfunction reference level for the reliability level of 60% (λ₆₀).

(JIS C5003)
The equation, λ₆₀=0.5×10⁻⁶/operation, indicates that the estimated malfunction rate is less than $\frac{1}{2,000,000}$ operations with a reliability level of 60%.





D
2
F

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Device & Module Solutions Company

Regional Contact

Americas
<https://components.omron.com/us>

Asia-Pacific
<https://components.omron.com/ap>

Korea
<https://components.omron.com/kr>

Europe
<https://components.omron.com/eu>

China
<https://components.omron.com.cn>

Japan
<https://components.omron.com/jp>