SIEMENS

Data sheet 5SL6116-7

Miniature circuit breaker 230/400 V 6kA, 1-pole, C, 16A



Model	
Product brand name	SENTRON
Product designation	Miniature circuit breaker
Design of the product	5SL miniature circuit breakers

General technical data	
Number of poles	1
Number of poles / Note	1P
Tripping characteristic class	C
circuit-breaker / Design	5SL6
Mechanical service life (switching cycles) / typical	10 000
Overvoltage category	3
Degree of pollution	2

Voltage	
Insulation voltage	
• with single-phase operation / at AC / rated value	250 V
• with multi-phase operation / at AC / rated value	440 V

Supply voltage

Subject to change without notice
© Copyright Siemens

Downloaded from Arrow.com.

Type of voltage	AC
Operating current / at AC / rated value	16 A
Supply voltage / at AC / rated value	400 V
Operating voltage	
• with multi-phase operation / at AC / maximum	440 V
• at DC / rated value / maximum	72 V
Supply voltage frequency	
• rated value	50 Hz

Protection class

Protection class IP	IP20, with connected conductors

Switching capacity

Switching capacity current	
• acc. to EN 60898 / rated value	6 kA
• acc. to IEC 60947-2 / rated value	6 kA
Energy limiting class	3

Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.8 W

Current

Tripping residual / rated value / derated current / at 40 Cel	15.23 A
Suitability for operation	Residential buildings/infrastructure

Product details

Product function / neutral conductor switching	No
Product feature / Touch protection	Yes
Product feature	
• halogen-free	Yes
• sealable	Yes
• silicon-free	Yes
Product extension / can be installed / supplementary devices	Yes

Connections

Connectable conductor cross-section / solid	
• minimum	0.75 mm²
• maximum	25 mm²
Connectable conductor cross-section / stranded	
• minimum	0.75 mm²
• maximum	25 mm²
Connectable conductor cross-section / finely stranded / with core end processing	
• minimum	0.75 mm²

© Copyright Siemens

Downloaded from Arrow.com.

• maximum	25 mm²
Tightening torque / with screw-type terminals	
• minimum	2.5 N·m
• maximum	3 N·m

Mechanical Design

Height	90 mm
Width	18 mm
Depth	76 mm
Installation depth	70 mm
Number of width units	1
Mounting position	any
Net weight	115 g

Environmental conditions

Influence of the surrounding temperature	Periodically +55°C, max. 95% humidity
Ambient temperature	
• minimum	-25 °C
• maximum	45 °C
Ambient temperature / during storage	
• minimum	-40 °C
• maximum	75 °C

Certificates

Reference code	
• acc. to DIN EN 61346-2	F
• acc. to DIN EN 81346-2	F

General Product Approval			Declaration of Conformity
CEBEC	VDE	TSE	EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,…)
http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SL6116-7

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/5SL6116-7


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SL6116-7

CAx-Online-Generator
http://www.siemens.com/cax

Tender specifications
http://www.siemens.com/specifications

Subject to change without notice
© Copyright Siemens

Downloaded from Arrow.com.



Subject to change without notice
© Copyright Siemens

Downloaded from Arrow.com.

Subject to change without notice
© Copyright Siemens

Downloaded from Arrow.com.