



Overview

Presentation	This unique Y cable takes a single C20 input and splits into two C13 outlets. This allows for multiple outputs to be connected to a single output on a rack PDU.
Lead time	Usually in Stock

Physical

Cable length	0.46 m
Depth	5.1 cm
Height	7.6 cm
Net weight	0.2 kg
Width	15.2 cm

Input

Plug standard	IEC 60320 C20
Max line current	15 A
Input current limits	15 A

Output

Number of power socket outlets	2 IEC 60320 C13
Output voltage	208 V

Conformance

Product certifications	UL listed
------------------------	-----------

Environmental

Ambient air temperature for operation	-10...40 °C
Relative humidity	20...80 %

Operating altitude	0...10000 ft
Ambient air temperature for storage	10...30 °C
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	0.27 kg
Package 1 Height	5.4 cm
Package 1 width	18.4 cm
Package 1 Length	16.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------