







Compliance: RohS III (2015/863/EU)

Tolerances: ≤ 10mm: ≥ 10mm:			Date	Name	DRR 60016			
			08/07	dr				
Material	02/21	dr						
Soldering conditions	01/11	dr						
IP rating	06/09	dr	knitter-switch		30 11 92		Page	
Operating temperature	11/08	dr					1/2	
Temperatures	01/08	dr						
Modifications	Date	Name						

Specifications:

Contact rating:	switching: 150mA, 42V DC non-switching: 200mA, 42V DC
Contact resistance:	80mOhm max.
Insulation resistance:	100MOhm min.
Mechanical life:	10 000 cycles
Operating force:	700gf max.
Operating temperature:	-40°C to +85°C
Storage temperature:	-40°C to +85°C
Soldering conditions:	pre-heat: max. 120°C, max. 70sec. wave soldering: max. 260°C, max. 10sec.
IP rating:	IP67
Material:	Cover: PA66, white O-ring: silicone, black Actuator: POM, gray PCB: epoxy Base: PA66, black Terminal / contact: phosphor bronze, min. 0.07µm gold plated over min. 0.1µm nickel

		Hexadecimal				
		Real coded				
		C	1	2	4	8
16 P o s i t i o n s	0	●				
	1	●	●			
	2	●		●		
	3	●	●	●		
	4	●			●	
	5	●	●		●	
	6	●		●	●	
	7	●	●	●	●	
	8	●				●
	9	●	●			●
	A	●		●		●
	B	●	●	●		●
	C	●			●	●
	D	●	●		●	●
	E	●		●	●	●
	F	●	●	●	●	●

Compliance: RohS III (2015/863/EU)

Tolerances: ≤ 10mm: ≥ 10mm:			Date	Name	DRR 60016		
			08/07	dr			
Material	02/21	dr			30 11 92		
Soldering conditions	01/11	dr					
IP rating	06/09	dr	knitter-switch				Page
Operating temperature	11/08	dr					2/2
Temperatures	01/08	dr					
Modifications	Date	Name					