

1

9.00

3

min.6

10

1.2^{+0.05}_{-0.10}

4

3.6

2

2.00

• (3.2^{+0.1}_{-0.3})

6

4.0

1.50

STE

STE

A

A

0.6±0.03

7

(10.5)

PCB

0.80

2.30

(3.1^{+0.1})

(1.6±0.2)

A-A

20:1

1.24±0.08

PCB-LAYOUT

Leiterplatten-Layout

5

2±0.05

NOTES:

BEMERKUNGEN:

1

1.27 μm - 2.54 μm Ni OVER THE COMPLETE LENGTH

1.27 μm - 2.54 μm Ni ueber die gesamte Laenge

2

0.8 μm - 1.8 μm Sn

0.8 μm - 1.8 μm Sn

3

1.0 μm - 3.0 μm Sn

1.0 μm - 3.0 μm Sn

4

Sn

Sn

5

RESTRING

UEBERSTAND

MIN. 50 μm

6

DIMENSION OF LOOSE PIECE

Mass fuer Einzelteil

7

ACCORDING TO EXECUTION INSTUCTION AUDI NO. N 905 854

Nach Ausfuehrungsvorschrift AUDI Nr. N 905 854

8

TO BE REELED ON PANCAKE REEL WITH INTERLEAVING PAPER

Pappspulen mit Zwischenlagenpapier

9

TO BE REELED ON PLASTIC REEL WITH INTERLEAVING PAPER

Kunststoffspulen mit Zwischenlagenpapier

10

0.8 μm - 2.0 μm Au

0.8 μm - 2.0 μm Au

DIRECTION OFF TOP OF REEL

1- -2

1- -3

2- -2

2- -3

8

9

2-1823233-3	A	Cu Sn 4	2 + 10 OVER ueber 1	9
2-1823233-2	A	Cu Sn 4	2 + 10 OVER ueber 1	8
1-1823233-3	A	Cu Sn 4	2 + 3 + 4 OVER ueber 1	9
1-1823233-2	A	Cu Sn 4	2 + 3 + 4 OVER ueber 1	8
TE PART NO	REV.	MATERIAL	SURFACE	REEL PACKAGING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

n. ISO 8015

n. ISO 2768-MS-E

0-PLC

±

1-PLC

±0.2

2-PLC

±0.1

3-PLC

±

4-PLC

±

ANGLES

±1°

FINISH

-

DWN

P. Nickelfeld

30OCT2008

CHK

J. Ryll

30OCT2008

APVD

-

PRODUCT SPEC

108-18706

APPLICATION SPEC

114-18379

WEIGHT

-

CUSTOMER DRAWING

SCALE

10:1

SHEET

1 OF 1

REV

A2

TE Connectivity

NAME

TAB 1.5x0.6 WITH ACTION PIN

Flachstecker 1.5x0.6 mit ACTION PIN

-

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=1823233

RESTRICTED TO

-

1471-9 (3/13)

Downloaded from [Arrow.com](#)