

➤ **DIMM-PC[®]/520-I** **DIMM-PC[®]/520-IU** **DIMM-PC[®]/520-IE**



original size

DIMM-PC[®]



- Full PC functionality at the size of a business card
- No active cooling required
- Comes along with all common PC interfaces
- Extreme compact size (40 x 67 x 6 mm)

➤ Product Overview

The DIMM-PC®/520-I is an extremely compact PC module to be plugged on to customized base boards. The new DIMM-PC®/520-I, based on AMD® Elan™ SC520 133 MHz, features high performance with an integrated floating point unit, up to 32 MByte DRAM and 32 MByte IDE compatible Flash. Due to the extreme low power design no active cooling is required. The integrated high functionality of a x86 CPU Module comes along with all common

PC interfaces (2xserial TTL, Printer, Keyboard, Floppy). The DIMM-PC® is widely used where stable performance is required but space and power consumption is limited. The new DIMM-PC®/520-IU offers one USB 1.1 port to address modern expansion devices. Ethernet is available at 10/100 Mbit performance with the DIMM-PC®/520-IE version. With a DIMM-PC® it's easy to substitute microcontroller applications with a flexible low cost PC based solution.

➤ Technical Information

Processor
AMD® Elan™ SC520 133MHz
DRAM
up to 32 MByte on board
Cache
16 kByte Write-Back L1
IDE compatible Flash Disk
up to 32 MByte on board
USB
optional 1x USB 1.1 OHCI
Ethernet
optional 10/100 MBit Ethernet
Serial ports
2x TTL (16550 compatible)
Floppy Interface
single drive
IDE Hard Disk Interface
on external device
Real Time Clock
integrated with chipset
Keyboard Controller
integrated with chipset

Other Features
Watchdog, JIDA Support, I²C Bus, Preinstalled DR-DOS, Programmable/CS Output, Support for alphanumerical displays
EEPROM
for CMOS Setup
Power Supply
5V
One Parallel Port
LPT1, EPP support
JRC
remote control via COM
Power Consumption
2 Watt @ 5V only
Dimensions
68 x 40 mm (2.7 x 1.6")
Temperature (*)
operation: 0° to 65°C, storage: -10° to 85°C
Humidity
operation: 10% to 90%, storage: 5% to 95%, (non condensing)

(*) Ask about wider temperature ranges

➤ Ordering Information

Article	Part.-No.	Description
DIMM-PC®/520-I	08012-1616-13-0	16 MByte DRAM, 16 MByte IDE compatible Flash Disk
DIMM-PC®/520-I	08012-3232-13-0	32 MByte DRAM, 32 MByte IDE compatible Flash Disk
DIMM-PC®/520-I	08012-3200-13-0	32 MByte DRAM, no IDE compatible Flash Disk
DIMM-PC®/520-IU	08012-3232-13-2	32 MByte DRAM, 32 MByte IDE compatible Flash Disk, USB controller
DIMM-PC®/520-IE	08012-3232-13-1	32 MByte DRAM, 32 MByte IDE compatible Flash Disk, 10/100 Mbit Ethernet
DIMM-PC®/KIT3	08005-0000-03-5	Starter Kit for DIMM-PC® with PC/104 interface (without DIMM-PC®)
DIMM-PC®/VGA2	08014-0000-00-0	VGA controller for CRT and LCD flatpanel
DIMM-PC®/ETH+COM	08006-0000-04-0	Ethernetcontroller & two serial interfaces
DIMM-PC®/COMB02 3.3 V	08014-0000-01-2	VGA, Ethernet and two serial interfaces, 3.3 V version
DIMM-PC®/Socket-CPU	SPCDIMM	Socket for DIMM-PC®, 144 Pin (80 pcs. packed)
DIMM-PC®/Socket-I/O	SIODIMM	Socket for DIMM-PC® I/O module 144 Pin (200 pcs. packed)

➤ Corporate Offices

Europe, Middle East & Africa

Oskar-von-Miller-Str. 1
85386 Eching/Munich
Germany
Tel.: +49 (0)8165/ 77 777
Fax: +49 (0)8165/ 77 219
sales@kontron.com

North America

14118 Stowe Drive
Poway, CA 92064-7147
USA
Tel.: +1 888 294 4558
Fax: +1 858 677 0898
sales@us.kontron.com

Asia Pacific

17 Building,Block #1,ABP.
188 Southern West 4th Ring Road
Beijing 100070,P.R.China
Tel.: + 86 10 63751188
Fax: + 86 10 83682438
kcn@kontron.cn

Kontron Embedded Modules

Brunnwiesenstr. 16
94469 Deggendorf
Germany
Tel.: +49 (0)991/ 370 24-100
Fax: +49 (0)991/ 370 24-333
sales@kontron.com