



THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.



ELECTRICAL CHARACTERISTICS @ 25° C

1.0 INDUCTANCE:		
(P2-P3)	350uH MIN. @ 0.1V, 100KHz, 8mA DC BIAS	
(P4-P5)	350uH MIN. @ 0.1V, 100KHz, 8mA DC BIAS	
(P7-P8)	350uH MIN. @ 0.1V, 100KHz, 8mA DC BIAS	
(P9-P10)	350uH MIN. @ 0.1V, 100KHz, 8mA DC BIAS	
2.0 TURNS RATIO:		
(P2-P3):(J1-J2)	1CT : 1CT ± 2%	
(P4-P5):(J3-J6)	1CT : 1CT ± 2%	
(P7-P8):(J4-J5)	1CT : 1CT ± 2%	
(P9-P10):(J7-J8)	1CT : 1CT ± 2%	
3.0 RETURN LOSS: 100 OHM REF.		
500kHz TO 40MHz	-18dB MIN.	
40MHz TO 100MHz	-12+20LOG(f/80MHz) MIN.	
4.0 INSERTION LOSS: RS=RL=100 OHMS		
100kHz TO 100MHz	-1.2dB MAX.	
5.0 GROSS TALK: Ch1-Ch2, Ch1-Ch3, Ch1-Ch4, Ch2-Ch3, Ch2-Ch4, Ch3-Ch4		
1MHz TO 30MHz	-35dB MIN.	
30MHz TO 80MHz	-24dB MIN.	
80MHz TO 100MHz	-25dB MIN.	
6.0 CM TO CM REJECTION:		
100kHz TO 100MHz	-30dB MIN.	
7.0 CM TO DM REJECTION:		
100kHz TO 100MHz	-35dB MIN.	
8.0 VOLTAGE WITHSTAND:		
(J1,J2) TO (P2,P3)	1500Vrms	
(J3,J6) TO (P4,P5)	1500Vrms	
(J4,J5) TO (P7,P8)	1500Vrms	
(J7,J8) TO (P9,P10)	1500Vrms	




9.0 THIS COMPNENT IS A PATENT PRODUCT;US PATENT NUMBER 7,123,117.





ORIGINATED BY	DATE	TITLE MagJack® TAB UP SHIELDED 10/100/100BT PATENTED	PART NO. / DRAWING NO.	STANDARD DIM.		[] METRIC DIM. AS REFERENCE		bel COMPONENTS FOR A CONNECTED PLANET
Zeng Xiao Chun	03-21-2011		SI-51009-F	TOL. IN INCH		UNIT : INCH [mm]	REV. : A1	
DRAWN BY	DATE		FILE NAME SI-51009-F.DWG	.X		SCALE : N/A	SIZE : A4	
Zhang Ru Sheng	03-21-2011			.XX			PAGE : 2	
				.XXX	±0.005			

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS
2002/95/EC



P.C.B. RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE
ALL CENTERLINE DIMENSIONS ARE BASIC



LED SPECIFICATION			
LED COLOR	WAVELENGTH	FORWARD V (MAX)	* (TYP)
GREEN	565 nm	2.5 V	2.2 V
YELLOW	590 nm	2.5 V	2.1 V


*WITH A FORWARD CURRENT OF 20 mA (TYP)

NOTES:


- CONNECTOR MATERIALS:
HOUSING: THERMOPLASTIC UL94 V-0
CONTACT/SHIELD: COPPER ALLOY
SHIELD PLATING: NICKEL OR TIN
CONTACT PLATING: SELECTIVE GOLD,
50 MICRO-INCHES MIN. IN CONTACT AREA.
- PIN NOT ELECTRICALLY CONNECTED MAYBE OMITTED.
SEE ELECTRICAL DRAWING FOR OMITTED PINS.
- TOLERANCES COMPLY WITH F.C.C. DIMENSION REQUIREMENTS.
- ALL TOLERANCES NOT OTHERWISE SPECIFIED TO BE ± 0.05 [0.13]
- REFLOW AND WAVE SOLDER COMPATIBLE -260°C FOR
10 SECONDS MAX.

ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM. TOL. IN INCH	[] METRIC DIM. AS REFERENCE	
					UNIT : INCH [mm]	REV. : A1
Zeng Xiao Chun	03-21-2011	MagJack® TAB UP SHIELDED 10/100/100BT PATENTED	SI-51009-F SI-51009-F.DWG	.X		SIZE : A4 PAGE : 3
DRAWN BY	DATE			.XX		
Zhang Ru Sheng	03-21-2011			.XXX		





SUGGESTED PANEL OPENING



1. THE SUGGESTED PANEL OPENING IS INTENDED TO GIVE THE USER THE ABILITY TO HAVE REASONABLE JACK / PANEL CLEARANCES YET MAINTAIN RELIABLE GROUNDING CAPABILITY.
2. ALL TOLERANCES NOT OTHERWISE SPECIFIED TO BE ± 0.005 [0.13]

ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM. TOL. IN INCH	[] METRIC DIM. AS REFERENCE	
Zeng Xiao Chun	03-21-2011	MagJack® TAB UP SHIELDED 10/100/100BT PATENTED	SI-51009-F	.X	UNIT : INCH [mm]	REV. : A1
DRAWN BY	DATE		FILE NAME	.XX	SCALE : N/A	SIZE : A4
Zhang Ru Sheng	03-21-2011		SI-51009-F.DWG	.XXX	±0.005	PAGE : 4