


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





PANDUIT P/N	WEIGHT
WMPLEFSE	.7 LBS/EACH 317 g/EACH


NOTES:

1. DESIGNED FOR MOUNTING ON 19" EIA RACKS.
2. COMPONENTS:
1- MANAGER
1- 17" DUAL HINGED COVER
4- #12-24 x 1/2" SCREWS
3. DIMENSIONS IN PARENTHESES ARE METRIC.

MAX STORAGE TEMPERATURE 65°C (149°F)
MAX OPERATING TEMPERATURE 60°C (140°F)



SURFACE IN CONTACT WITH FRONT OF THE RACK RAIL



TITLE					
WMPLEFSE HORIZONTAL MANAGER					
CUSTOMER DRAWING					
ITEM REVISION NAME			V10101LF/06		
DATASET FILE NAME			V10101LF_DC/06B		
			THIRD ANGLE PROJECTION		
MATERIAL			ABS		
DRAWN BY			JDWE		
DATE			12-17-02		
CHK			MECA		
SCALE			NONE		
DRAWING NUMBER			10101-20		
SHEET 1 OF 1			A		

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
06B	5-11-20	JBO	JCO	JEFK	ADDED TEMPERATURE NOTE	M09000LT