




used for: D-SUB

AT ALL TIMES WATER RESISTANT CONNECTORS NOT IN USE MUST BE COVERED WITH A CONEC WATER RESISTANT CAP OR WATER TIGHT HOOD TO REACH WATER TIGHTNESS.

No. of pos.	A ^{+0.2}	B ^{+0.2}	C	D ^{-0.25}	PART NO.
9	21.1	39.4	25.00 ^{+0.12} _{-0.13}	16.46	6STD09SAM99B30X
15	21.1	47.7	33.30 ^{+0.15} _{-0.1}	24.79	6STD15SAM99B30X
25	21.1	61.4	47.04 ^{±0.13}	38.50	6STD25SAM99B30X
37	21.1	77.9	63.50 ^{±0.13}	54.96	6STD37SAM99B30X



- NOTES:
- METALSHELLS: COPPER ALLOY; min. 320µ" TIN
 - INSULATORS: PBT GF UL 94 V-0, BLACK
 - CONTACTS: COPPER ALLOY
PLATING: 8µ" HARD GOLD OVER min. 50µ" NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
 - THREADED INSERT: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
 - COLLAR: COPPER ALLOY; min. 200µ" TIN over 80µ" NICKEL
 - FRAME: ZINC DIECAST; NICKEL PLATED
 - HEXLOCKING SCREW: STAINLESS STEEL
 - MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
 - CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance		
2004	date	name
drawn	26.11.	Lehmenkühler
appd.	26.11.	Mickenbecker
norm	DIN 41652	
d-old		
CONEC®		

scale: 2:1	
material: SEE NOTES	
title: D-SUB FEMALE 9-37pos. SOLDER CUP with threaded insert and hexlocking screw	
dwg no:	AutoCAD 2004 18K1A316
part no:	SEE TABLE
DIN-A 3 sh: 1/1	