

<https://www.wago.com/811-316>



Fuse terminal block, 811 Series, light gray

Easily, quickly and safely connect conductors with this fuse terminal block (item number 811-316). Strip lengths must be between 12 mm and 13 mm when connecting conductors to this fuse terminal block. Featuring conductor terminals along with CAGE CLAMP®, this connector is highly versatile. Our proven universal connection known as CAGE CLAMP® is industry-leading when it comes to connection technology and electrical interconnections. Depending on the type of conductor, this fuse terminal block is suitable for conductor cross sections ranging from 2.5 mm² to 16 mm². It has one level. You can connect a single potential / one pole using the two clamping points. The light gray housing is made of polyamide (PA66) for insulation. These function terminal blocks are mounted using DIN-35 rails..

Safety Information

The fuse holder must not be opened under load.

Ratings per	IEC/HD 60269-2		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	1000 V	-	-
Rated surge voltage	8 kV	-	-
Rated current	32 A	-	-

Ratings (note)	Electrical ratings are specified in the technical data of both fuse terminal block and fuse. When selecting glass cartridge fuses, make sure that the listed power loss is not exceeded.
----------------	--

Use group	B	C	D
Rated voltage	-	-	-

Use group	B	C	D
Rated voltage	-	-	-

Maximum power loss P_{loss} of fuse insert for overload and short-circuit protection (individual arrangement)	3 W
Maximum power loss P_{loss} of fuse insert for overload and short-circuit protection (block arrangement)	3 W
Power loss P_i max. short-circuit protection (individual arrangement)	3 W
Power loss P_{loss} (max.) of fuse cartridge for short-circuit protection (block arrangement)	3 W

Voltage type 1	DC
Fuse receptacle	pluggable
Fuse type	Cylindrical fuse; 10 x 38 mm; for photo-voltaic applications



Connection data																		
Clamping units	2	Connection 1 <table><tr><td>Connection technology</td><td>CAGE CLAMP®</td></tr><tr><td>Actuation type</td><td>Operating tool</td></tr><tr><td>Connectable conductor materials</td><td>Copper</td></tr><tr><td>Solid conductor</td><td>2.5 ... 16 mm² / 14 ... 6 AWG</td></tr><tr><td>Fine-stranded conductor</td><td>2.5 ... 16 mm² / 14 ... 6 AWG</td></tr><tr><td>Strip length</td><td>12 ... 13 mm / 0.47 ... 0.51 inches</td></tr><tr><td>Pole number</td><td>1</td></tr><tr><td>Wiring direction</td><td>Side-entry wiring</td></tr></table>	Connection technology	CAGE CLAMP®	Actuation type	Operating tool	Connectable conductor materials	Copper	Solid conductor	2.5 ... 16 mm² / 14 ... 6 AWG	Fine-stranded conductor	2.5 ... 16 mm² / 14 ... 6 AWG	Strip length	12 ... 13 mm / 0.47 ... 0.51 inches	Pole number	1	Wiring direction	Side-entry wiring
Connection technology	CAGE CLAMP®																	
Actuation type	Operating tool																	
Connectable conductor materials	Copper																	
Solid conductor	2.5 ... 16 mm² / 14 ... 6 AWG																	
Fine-stranded conductor	2.5 ... 16 mm² / 14 ... 6 AWG																	
Strip length	12 ... 13 mm / 0.47 ... 0.51 inches																	
Pole number	1																	
Wiring direction	Side-entry wiring																	
Total number of potentials	1																	
Number of levels	1																	

Physical data		
Width		17.5 mm / 0.689 inches
Height		105 mm / 4.134 inches
Depth from upper-edge of DIN-rail		55 mm / 2.165 inches

Mechanical data		
Mounting type		DIN-35 rail
Mounting (note)		The fixed foot of the fuse terminal block must face upwards so that the fuse cannot fall out.

Material data		
Note (material data)		Information on material specifications can be found here
Color		light gray
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0 MJ
Weight		63.5 g

Environmental requirements		
Processing temperature		-35 ... +85 °C
Continuous operating temperature		-35 ... +85 °C

Commercial data		
PU (SPU)		12 pcs
Packaging type		Box
Country of origin		CN
GTIN		4050821849001
Customs tariff number		85369095000



Product Classification	
UNSPSC	39121624
eCl@ss 10.0	27-14-11-16
eCl@ss 9.0	27-14-11-16
ETIM 9.0	EC002705
ETIM 8.0	EC002705
ECCN	EAR99

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Approvals / Certificates	
Declarations of conformity and manufacturer's declarations	

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 811-316	

Documentation			
Bid Text			
811-316	19.02.2019	xml 3.72 KB	
811-316	14.03.2017	doc 27.00 KB	

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 811-316	EPLAN Data Portal 811-316
	WSCAD Universe 811-316
	ZUKEN Portal 811-316



1 Compatible Products

1.1 Optional Accessories

1.1.1 Ferrule

1.1.1.1 Ferrule



Item No.: 216-209
Ferrule; Sleeve for 10 mm² / AWG 8; insulated; electro-tin plated; red



Item No.: 216-109
Ferrule; Sleeve for 10 mm² / AWG 8; uninsulated; electro-tin plated



Item No.: 216-208
Ferrule; Sleeve for 6 mm² / AWG 10; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; yellow



Item No.: 216-108
Ferrule; Sleeve for 6 mm² / AWG 10; uninsulated; electro-tin plated; silver-colored



Item No.: 216-545
Twin ferrule; Sleeve for 2 x 2.5 mm / AWG 14; insulated; blue



Item No.: 216-546
Twin ferrule; Sleeve for 2 x 4 mm / AWG 12; insulated; gray



Item No.: 216-547
Twin ferrule; Sleeve for 2 x 6 mm / AWG 10; insulated; yellow

1.1.2 Installation

1.1.2.1 Locking system



Item No.: 811-612
Coupling kit; for 12 poles; red

1.1.3 Jumper

1.1.3.1 Jumper



Item No.: 811-480
Jumper; 10-way; insulated; light gray



Item No.: 811-481
Jumper; 11-way; insulated; light gray



Item No.: 811-482
Jumper; 12-way; insulated; light gray



Item No.: 811-472
Jumper; 2-way; insulated; light gray



Item No.: 811-473
Jumper; 3-way; insulated; light gray



Item No.: 811-474
Jumper; 4-way; insulated; light gray



Item No.: 811-475
Jumper; 5-way; insulated; light gray



Item No.: 811-476
Jumper; 6-way; insulated; light gray



Item No.: 811-477
Jumper; 7-way; insulated; light gray



Item No.: 811-478
Jumper; 8-way; insulated; light gray



Item No.: 811-479
Jumper; 9-way; insulated; light gray

1.1.4 Marking

1.1.4.1 Label



Item No.: 210-805
Labels; for Smart Printer; permanent adhesive; 6 x 15 mm; 3000 pieces on roll; white



Item No.: 210-805/000-002
Labels; for Smart Printer; permanent adhesive; 6 x 15 mm; 3000 pieces on roll; yellow



Item No.: 210-806
Labels; for Smart Printer; permanent adhesive; 9 x 15 mm; 3000 pieces on roll; white



Item No.: 210-806/000-002
Labels; for Smart Printer; permanent adhesive; 9 x 15 mm; 3000 pieces on roll; yellow



Item No.: 210-705
Labels; for TP printers; permanent adhesive; 6 x 15 mm; 3000 pieces on roll; white



Item No.: 210-705/000-002
Labels; for TP printers; permanent adhesive; 6 x 15 mm; 3000 pieces on roll; yellow



Item No.: 210-706
Labels; for TP printers; permanent adhesive; 9 x 15 mm; 3000 pieces on roll; white



Item No.: 210-706/000-002
Labels; for TP printers; permanent adhesive; 9 x 15 mm; 3000 pieces on roll; yellow



1.1.4.2 Marker



Item No.: 793-5501/000-006
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; blue



Item No.: 793-5501/000-014
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; brown



Item No.: 793-5501/000-007
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; gray



Item No.: 793-5501/000-023
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; green



Item No.: 793-5501/000-017
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; light green



Item No.: 793-5501/000-012
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; orange



Item No.: 793-5501/000-005
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; red



Item No.: 793-5501/000-024
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; violet



Item No.: 793-5501
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 793-5501/000-002
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; yellow



Item No.: 793-501/000-006
WMB marking card; as card; not stretchable; plain; snap-on type; blue



Item No.: 793-501/000-007
WMB marking card; as card; not stretchable; plain; snap-on type; gray



Item No.: 793-501/000-023
WMB marking card; as card; not stretchable; plain; snap-on type; green



Item No.: 793-501/000-017
WMB marking card; as card; not stretchable; plain; snap-on type; light green



Item No.: 793-501/000-012
WMB marking card; as card; not stretchable; plain; snap-on type; orange



Item No.: 793-501/000-005
WMB marking card; as card; not stretchable; plain; snap-on type; red



Item No.: 793-501/000-024
WMB marking card; as card; not stretchable; plain; snap-on type; violet



Item No.: 793-501
WMB marking card; as card; not stretchable; plain; snap-on type; white



Item No.: 793-501/000-002
WMB marking card; as card; not stretchable; plain; snap-on type; yellow



Item No.: 2009-115/000-006
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue



Item No.: 2009-115/000-007
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray



Item No.: 2009-115/000-023
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green



Item No.: 2009-115/000-017
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; light green



Item No.: 2009-115/000-012
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange



Item No.: 2009-115/000-005
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red



Item No.: 2009-115/000-024
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet



Item No.: 2009-115
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 2009-115/000-002
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow

1.1.4.3 Marker carrier



Item No.: 285-442
Adaptor; gray

1.1.5 Supply module

1.1.5.1 Supply module



Item No.: 811-471
Supply module; 35 mm²; for 811 Series Fuse Terminal Blocks; SCREW CLAMP CONNECTION; 35,00 mm²; light gray

1.1.6 Test and measurement

1.1.6.1 Testing accessories




Item No.: 206-912
WAGO Test Probes; 2 mm Ø; 1000 V; CAT IV; 10 A

Installation Notes

Installation



Creating a 2- or 3-pole fuse terminal block via coupling kit.




Removing a terminal block from the DIN-rail.


Conductor termination



Open and close lever via operating tool.



CAGE CLAMP® connection
Inserting a conductor.
Opening the clamping unit via integrated lever.



Terminating ferruled conductors up to 10 mm² (8 AWG).

Commoning




Jumper bar for quick and convenient commoning



Inserting a fuse.

Marking



WMB marker slot for convenient identification



Marker carriers (285-442) for continuous marking strips