


TAC/TAH series (50,60,80,100,150A)

TAC **-50** **-223** **-**

① ② ③ ④

① ② ③ ④



- ① Series Name
② Rated Current
③ Line to ground capacitor code: Refer to table 1.1.

table1.1 Line to ground capacitor code

Code	Leakage Current (Input 250/500V 60Hz)	Line to ground capacitor (nominal value)
103	1.0mA/2.0mA max	10,000pF
223	2.5mA/5.0mA max	22,000pF
333	3.5mA/7.0mA max	33,000pF

*When the line to ground capacitor code is different, the attenuation characteristic is different.

- ④ Option
U: Improve differential mode attenuation
(Rated voltage 250V)

Features of TAC/TAH series

- **Three phase rated voltage 500VAC (voltage range:528V max) (1-Stage filter)**
- **Selectable leakage current value**

■ **TAC: High-attenuation type from 150kHz to 1MHz**

■ **TAH:** Ultra high-attenuation type from 9kHz to 1MHz


Specifications

No.	Items	TAC-50-223	TAC-60-223	TAC-80-223	TAC-100-223	TAC-150-223
		TAH-50-223	TAH-60-223	TAH-80-223	TAH-100-223	TAH-150-223
1	Rated Voltage[V]	AC Three Phase 500 (voltage range:528 max) 50/60Hz *1				
2	Rated Current[A]	50	60	80	100	150
3	Test Voltage (Terminal-Mounting Plate)	2,500 VAC (Cutoff Current = 100mA), 1minute at room temperature and humidity				
4	Isolation Resistance (Terminal-Mounting Plate)	500 VDC 100MΩ min at room temperature and humidity				
5	Leakage current	Refer to table 1.1				
6	DC resistance	7mΩ max	5mΩ max	5mΩ max	4mΩ max	3mΩ max
7	Safety agency approval temperatures	-25 to +85℃ (Refer to Derating Curve)				
8	Operating temperature	-40 to +85℃ (Refer to Derating Curve)				
9	Operating humidity	20 to 95%RH (Non condensing)				
10	Storage temperature/humidity	-40 to +85℃/20 to 95%RH (Non condensing)				
11	Vibration	10 to 55Hz, 19.6m/s² (2G), 3min. Period, 1hour each X, Y and Z axis				
12	Impact	196.1m/s² (20G), 11ms Once each X, Y and Z axis				
13	Safety agency approvals	UL1283, CSA C22.2 No.8 (C-UL) , DIN EN60939 VDE0565 Teil3-1, ENEC				
14	Case size (without projection)	90×54×179 mm (W×H×D)		140×85×267 mm (W×H×D)		170×92×285 mm (W×H×D)
		[3.54×2.13×7.05 inches]		[5.51×3.35×10.51 inches]		[6.69×3.62×11.22 inches]
15	Weight	1.4kg max		3.8kg max		4.8kg max


*1 Only "TAC/TAH-□□□-□□□-U", Three Phase 250 (275 max)

Circuit Diagram


(1) TAC--



(2) TAC-□□□-□□□-U (Option : U)




Derating Curve



*Keep free ventilation holes for cooling.

External view


TAC-50-□□□ / TAC-60-□□□
TAH-50-□□□ / TAH-60-□□□



※ Can not be mounted upside-down.
(mounted the top surface)

※ Tolerance : ± 1 [± 0.04]
 ※ Weight : 1.4kg max
 ※ Mounting Plate : Iron (surface finishing:nickel plating) $t=1.2$ [0.05]
 ※ Case : PBT
 ※ Dimensions in mm, []=inches
 ※ Terminal block screw tightening torque M5:3.0N · m (30.7kgf · cm) max
 ※ Protection Earth screw tightening torque M4:1.6N · m (16.9kgf · cm) max

TAC-80-□□□ / TAC-100-□□□
TAH-80-□□□ / TAH-100-□□□



※ Can not be mounted upside-down.
(mounted the top surface)

※ Tolerance : ± 1 [± 0.04]
 ※ Weight : 3.8kg max
 ※ Chassis Material : Stainless steel $t=1.0$ [0.04]
 ※ Dimensions in mm, []=inches
 ※ Terminal block screw tightening torque M8:9.2N · m (93.9kgf · cm) max
 ※ Protection Earth screw tightening torque M6:5.8N · m (59.2kgf · cm) max

External view

TAC-150-□□□
TAH-150-□□□

