molex



Part Number : 1202310102
Product Description : Brad M23 Signal Connector, Back Panel-Mount Receptacle, Straight Male Single Hole Mount M25x1.5, Crimp Contacts, 9 (8+1) Poles
Series Number : 120231
Status : Obsolete
Product Category : Circular Industrial Connectors
Engineering Part Number : KRS9P46-410

Documents and Resources

Drawings

1202310102_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Obsolete

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Circular Industrial Connectors
Series	120231
Description	Brad M23 Signal Connector, Back Panel-Mount Receptacle, Straight Male Single Hole Mount M25x1.5, Crimp Contacts, 9 (8+1) Poles
Comments	Crimp Range 0.14-1.00mm² / 0.75-2.50mm²
IP Rating	IP67
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906300876

Electrical

Current - Maximum per Contact	20.0A, 8.0A
Voltage - Maximum	300V

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	1.000/g
Orientation	Straight

Obsolete

Downloaded from Arrow.com.

Poles	9 (8+1)
Temperature Range - Operating	-40° to +125°C
Wire Size (AWG)	N/A

Obsolete

Downloaded from Arrow.com.