

3249059

<https://www.phoenixcontact.com/us/products/3249059>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mini flange terminal block, can be combined with D-MSBV 2,5-F and MSBV 2,5-M, nom. voltage: 800 V, nominal current: 24 A, number of connections: 2, connection method: Spring-cage connection, Rated cross section: 2.5 mm<sup>2</sup>, 1 level, cross section: 0.08 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: direct screw connection, color: gray

Your advantages

- Space saving thanks to compact design and mounting option on a 15 mm DIN rail
- Clear arrangement thanks to marking of all terminal points

Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3249059             |
| Packing unit                         | 50 pc               |
| Minimum order quantity               | 50 pc               |
| Sales key                            | BE02                |
| Product key                          | BE2165              |
| Catalog page                         | Page 303 (C-3-2013) |
| GTIN                                 | 4046356166508       |
| Weight per piece (including packing) | 3.46 g              |
| Weight per piece (excluding packing) | 3.05 g              |
| Customs tariff number                | 85369010            |
| Country of origin                    | CN                  |

# MSBV 2,5-F - Mini flange terminal block



3249059

<https://www.phoenixcontact.com/us/products/3249059>

## Technical data

### Product properties

|                       |                          |
|-----------------------|--------------------------|
| Product type          | Miniature terminal block |
| Number of connections | 2                        |
| Number of rows        | 1                        |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                                                 |        |
|-------------------------------------------------|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 0.77 W |

### Connection data

|                                 |         |
|---------------------------------|---------|
| Number of connections per level | 2       |
| Nominal cross section           | 2.5 mm² |

### 1 level

|                                                                                           |                                           |
|-------------------------------------------------------------------------------------------|-------------------------------------------|
| Stripping length                                                                          | 8 mm                                      |
| Connection in acc. with standard                                                          | IEC 60947-7-1                             |
| Conductor cross section rigid                                                             | 0.08 mm² ... 4 mm²                        |
| Cross section AWG                                                                         | 28 ... 12 (converted acc. to IEC)         |
| Conductor cross section flexible                                                          | 0.08 mm² ... 2.5 mm²                      |
| Conductor cross section, flexible [AWG]                                                   | 28 ... 14 (converted acc. to IEC)         |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm² ... 2.5 mm²                      |
| Flexible conductor cross section (ferrule with plastic sleeve)                            | 0.14 mm² ... 2.5 mm²                      |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm²                                   |
| Nominal current                                                                           | 24 A                                      |
| Maximum load current                                                                      | 30 A (with 4 mm² conductor cross section) |
| Nominal voltage                                                                           | 800 V                                     |
| Nominal cross section                                                                     | 2.5 mm²                                   |
| Connection in acc. with standard                                                          | IEC/EN 60079-7                            |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
|---------------------|--|

# MSBV 2,5-F - Mini flange terminal block



3249059

<https://www.phoenixcontact.com/us/products/3249059>

|                 |        |
|-----------------|--------|
| Width           | 5.2 mm |
| End cover width | 4 mm   |
| Height          | 32 mm  |
| Depth           | 20 mm  |
| Hole diameter   | 3.2 mm |

## Material specifications

|                                                                         |                 |
|-------------------------------------------------------------------------|-----------------|
| Color                                                                   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group                                               | I               |
| Insulating material                                                     | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 9.8 kV      |
| Result                | Test passed |

### Temperature-rise test

|                                                  |                                     |
|--------------------------------------------------|-------------------------------------|
| Requirement temperature-rise test                | Increase in temperature $\leq 45$ K |
| Result                                           | Test passed                         |
| Short-time withstand current 2.5 mm <sup>2</sup> | 0.3 kA                              |
| Short-time withstand current 4 mm <sup>2</sup>   | 0.48 kA                             |
| Result                                           | Test passed                         |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 2 kV        |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Mechanical tests

# MSBV 2,5-F - Mini flange terminal block



3249059

<https://www.phoenixcontact.com/us/products/3249059>

## Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## Test for conductor damage and slackening

|                                |                               |
|--------------------------------|-------------------------------|
| Rotation speed                 | 10 rpm                        |
| Revolutions                    | 135                           |
| Conductor cross section/weight | 0.08 mm <sup>2</sup> / 0.1 kg |
|                                | 2.5 mm <sup>2</sup> / 0.7 kg  |
|                                | 4 mm <sup>2</sup> / 0.9 kg    |
| Result                         | Test passed                   |

## Environmental and real-life conditions

### Aging

|                    |             |
|--------------------|-------------|
| Temperature cycles | 192         |
| Result             | Test passed |

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |                                                  |
|------------------------|--------------------------------------------------|
| Specification          | DIN EN 50155 (VDE 0115-200):2008-03              |
| Spectrum               | Long life test category 1, class B, body mounted |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$   |
| ASD level              | 0.02g <sup>2</sup> /Hz                           |
| Acceleration           | 0.8g                                             |
| Test duration per axis | 5 h                                              |
| Test directions        | X-, Y- and Z-axis                                |
| Result                 | Test passed                                      |

### Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 5g                                  |
| Shock duration                 | 30 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

### Ambient conditions

|                                         |                                                                                                                              |
|-----------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation)         | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                                                    |
| Ambient temperature (assembly)          | -5 °C ... 70 °C                                                                                                              |
| Ambient temperature (actuation)         | -5 °C ... 70 °C                                                                                                              |

# MSBV 2,5-F - Mini flange terminal block



3249059

<https://www.phoenixcontact.com/us/products/3249059>

|                                          |               |
|------------------------------------------|---------------|
| Permissible humidity (operation)         | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

## Standards and regulations

|                                  |                |
|----------------------------------|----------------|
| Connection in acc. with standard | IEC 60947-7-1  |
|                                  | IEC/EN 60079-7 |

## Mounting

|               |                         |
|---------------|-------------------------|
| Mounting type | direct screw connection |
|---------------|-------------------------|

# MSBV 2,5-F - Mini flange terminal block


3249059

<https://www.phoenixcontact.com/us/products/3249059>



## Drawings

Dimensional drawing



# MSBV 2,5-F - Mini flange terminal block

3249059

<https://www.phoenixcontact.com/us/products/3249059>



Circuit diagram



# MSBV 2,5-F - Mini flange terminal block



3249059

<https://www.phoenixcontact.com/us/products/3249059>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3249059>

|                                                                                                                    |                       |                       |                   |                             |
|--------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                             |
|                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                        | 600 V                 | 20 A                  | 28 - 12           | -                           |
| Use group C                                                                                                        | 600 V                 | 20 A                  | 28 - 12           | -                           |
| Use group D                                                                                                        | 600 V                 | 20 A                  | 28 - 12           | -                           |

|                                                                                                                                    |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>IECEE CB Scheme</b><br>Approval ID: DE1-62820 |                       |                       |                   |                             |
|                                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                    | 800 V                 | 24 A                  | -                 | 0.2 - 2.5                   |

|                                                                                                                                     |  |  |  |  |
|-------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|  <b>EAC</b><br>Approval ID: RU C-DE.BL08.B.00644 |  |  |  |  |
|-------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|

|                                                                                                                                            |                       |                       |                   |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>VDE Zeichengenehmigung</b><br>Approval ID: 40029769 |                       |                       |                   |                             |
|                                                                                                                                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                            | 800 V                 | 24 A                  | -                 | 0.2 - 2.5                   |

|                                                                                                                                    |                       |                       |                   |                             |
|------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                             |
|                                                                                                                                    | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                                        | 600 V                 | 20 A                  | 28 - 12           | -                           |
| Use group C                                                                                                                        | 600 V                 | 20 A                  | 28 - 12           | -                           |
| Use group D                                                                                                                        | 600 V                 | 5 A                   | 28 - 12           | -                           |

|                                                                                                                                   |  |  |  |  |
|-----------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|
|  <b>EAC</b><br>Approval ID: KZ7500651131219505 |  |  |  |  |
|-----------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|



# MSBV 2,5-F - Mini flange terminal block



3249059

<https://www.phoenixcontact.com/us/products/3249059>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# MSBV 2,5-F - Mini flange terminal block



3249059

<https://www.phoenixcontact.com/us/products/3249059>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)