

CHAMP 0.8mm Centerline Connector Backshell Kits

Standard


With Squeeze-to-Release Latches

Material and Finish

Backshells — Steel, plated .000197 [0.005] min. bright tin-lead over .000098 [0.0025] min. copper

Spring Latches — Stainless Steel

Spring Latch Covers — UL 94V-0 rated, ABS/PC alloy, black



No. of Positions	Dimensions			Part Nos.
	A	B	C	Bulk Kits (100 Assemblies)
36	1.197 30.40	.754 19.15	.394 10.00	787231-1
50	1.417 36.00	.974 24.75	.433 11.00	787133-1
68	1.701 43.20	1.258 31.95	.442 11.22	787229-1

With Jackscrew Fastener


Material and Finish

Backshells — Steel, plated .000197 [0.005] min. bright tin-lead over .000098 [0.0025] min. copper

Jackscrews — Steel, plated blue chromate over zinc

Jackscrew Head — ABS/PC, black

Jackscrew Covers — UL 94V-0 rated, ABS/PC alloy, black



No. of Positions	Dimensions			Part Nos.
	A	B	C	Bulk Kits (100 Assemblies)
50	1.417 36.00	.974 24.75	.433 11.00	787233-1
68	1.701 43.20	1.258 31.95	.442 11.22	787191-1

Note: Recommended wire size — 30 AWG [0.05mm²], insulation diameter range — .022-.025 [0.56-0.64]

Wire must be approved by Tyco Electronics.