


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-14-010938	18JUL2014	DD	RL
	A1	REVISED PER ECO-16-013871	21SEP2016	DD	RL







SECTION A-A




Ø26.58
MIN FEED THROUGH CONDITION
(1mm CLEARANCE ALL THE WAY
AROUND INCLUDED)


1. MATERIAL IDENTIFICATION SYMBOLS.
2. 0.2 mm MAXIMUM RADIUS PERMISSIBLE ON EDGES AND FILLETS SHOWN AS SHARP FOR PLASTIC PARTS.
3. PRODUCTION DATE CODE (YY-DDD-HH) AND ASSEMBLY PART NUMBER APPLIED IN APPROXIMATE LOCATION.
4. TOOL CAVITY NUMBER
5. COMPANY LOGO
6. TERMINAL CAVITY IDENTIFICATION NUMBER.
7. FOLLOW TE# 408-32134 FOR PROPER SPACER ENGAGEMENT.










SECTION B-B














SCALE 3:1



2272431-4	2272431-3	2272431-2	2272431-1	<-------- ASSEMBLY PART NUMBER			
1	1	1	1	SPACER	>PBT+PC-GF30<	RED	2
1				HOUSING, KEY D	>PA66-GF35<	BLACK	1
	1			HOUSING, KEY C	>PA66-GF35<	BLACK	1
		1		HOUSING, KEY B	>PA66-GF35<	BLACK	1
			1	HOUSING, KEY A	>PA66-GF35<	BLACK	1
QTY REQ'D PER ASSY				DESCRIPTION	MATERIAL	COLOR	ITEM

PARTS LIST

KEYING OPTIONS

			
2272431-1	2272431-2	2272431-3	2272431-4
KEYING OPTION "A"	KEYING OPTION "B"	KEYING OPTION "C"	KEYING OPTION "D"

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
FINISH -

DWN D. DRUMMOND 02APR2014
CHK R. LACUESTA 02APR2014
APVD R. LACUESTA 02APR2014
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME PLUG ASSEMBLY, IX6 UNSEALED, SIDE LATCH

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2272431	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV A1

4805 (3/13)

Downloaded from Arrow.com.