



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'HSTT75-CC'

Your search criteria matched only one product, shown below

HSTT75-CC



- Flexible Ployolefin DRY-SHRINK™Heat Shrink Tubing
- General Purpose heat shrink tubing for dry locations
 - Applications include insulating, protecting, harnessing and identifying wires.
 - Material Type: Crosslinked Polyolefin
 - Shrink Ratio: 2:1
 - Temperature Range: -67°F to 275°F (-55°C to 135°C)
 - Flammability Rating: Flame retardant EXCEPT clear
 - Voltage: 600 V
 - UL Recognized, CSA Certified
 - Mil Spec: AMSDTL-23053/5 Class 1 (Colors) Class 2 (Clear)

	Part Number	HSTT75CC
	RoHS Compliancy Status	Compliant
	Part Description	Thin Wall Polyolefin Heat Shrink
	Material	Polyolefin cross-linked
	Color	Clear
	Military Specification	AMS-DTL-23053/5 Class 2
	Length Per Reel (ft.)	100
	Length Per Reel (m)	30.5
	Max. Recovered I.D. (In.)	.375
	Max. Recovered I.D. (mm)	9.5
	Min. Expanded I.D. (In.)	.750
	Min. Expanded I.D. (mm)	19.0
	Nominal Diameter / Size	.750
	Nominal Recovered Wall Thickness (In.)	.030
	Nominal Recovered Wall Thickness (mm)	.8
	Pricing Description	Heat Shrink Thin, .75"(19.0mm) Dia, Clear
	Shrink Ratio	2:1
	Temperature Range	-67°F to 275°F (-55°C to 135°C)
	Min. Order UOM	RL
	Min. Order Qty.	1
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.