
Representative Image

Catalog No. TY533M

Description: CBL TIE 18LB 4IN NAT NYL MTG HOLE

UPC No 786210825502

Home > Wire & Cable Management > Ty-Rap > Mounted Head Ties

Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 91mm (3.6 Inches), Width of 2.5mm (0.1 Inches), Thickness of 1mm (0.04 Inches), Tensile Strength Rating of 80 Newtons (18 pounds), #4 Screw for Mounting

Descriptors

Category	Mounted Head Ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.1 in , 2.5 mm
Length	3.6 in , 91 mm
Thickness	0.04 in , 1 mm
Bundle Diameter	0.08 to 0.63 in , 2 to 16 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

by ABB

Downloaded from Arrow.com.

ETIM	EC000046 Cable tie
Band width	2.5 mm
Length belt/tape/tie	91 mm
Length belt/tape/tie	3.6 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	16 mm
Min. holding force	80 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
Type of fastening	Screw hole
VG approval	N
MIL approval	N
UL approval	N

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.