Part Number : 768505038
Product Description : Impact 100 Ohm 4 Pair Right-Angle Orthogonal Daughtercard, Right Guide, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free
Series Number : 76850
Status : Active
Product Category : Backplane Connectors



Documents and Resources

Drawings

768505038_sd.pdf

PK-70873-610-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

SYM-76850-5038-001.zip

EE-76850-049-001.pdf

EE-76850-055-001.pdf

SP-76850-049-001.zip

SP-76850-055-001.zip

Specifications

AS-76060-9999-001.pdf

AS-76850-990-001.pdf

PS-76060-999-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006

Downloaded from Arrow.com.

EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	76850
Description	Impact 100 Ohm 4 Pair Right-Angle Orthogonal Daughtercard, Right Guide, 8 Columns, 96 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free
Application	Daughtercard, Orthogonal, Orthogonal Direct, Orthogonal Midplane
Component Type	PCB Receptacle
Product Name	Impact
UPC	884982186200

Agency

Downloaded from Arrow.com.

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shielded	No
Shield Type	N/A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	96
Circuits (maximum)	96
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	13.190/g
Number of Columns	8
Number of Pairs	4
Number of Rows	12
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.20mm
Pitch - Mating Interface	1.90mm, 2.15mm

Downloaded from Arrow.com.

Pitch - Termination Interface	1.90mm, 2.15mm
Plating min - Mating	0.762µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 100 Ohm 4 Pair Vertical Orthogonal Headers	76845

Application Tooling

Downloaded from Arrow.com.