

Data sheet

Page 2/7

M12 Panel feed through adapters, X-coded, to RJ45 - straight

P/N

MWN811A415

EAN 4250184157441

2026/08/21

Version: O

Technical Data

General Data

Electromagnetic measurement according to MICE	E2
Design	Jack
Mounting style	back side
Shielding	shielded
Transmission technology	Copper
Color	metallike
Dimensions	
Dimension (L x W x H)	46.35 mm x 21.6 mm x 29 mm
Dimension (L x W x H)	1.825 in. x 0.85 in. x 1.142 in.
Labeling option	on housing

Transmission characteristics

Category (ISO)	6 _A
Category (TIA)	6A
Transmission rate up to 10 GBit	IEEE 802.3an

Connections/interfaces

Connector technology interface 1	RJ45-jack
Connector technology interface 2	M12-jack
Coding interface 2	X-coded
Number of ports interface 1	1
Number of ports interface 2	1
Number of equipped ports interface 1	1
Number of ports interface 2 equipped	1
Number of positions/contacts interface 1	8P/8C
Number of positions/contacts interface 2	8
Cable access/outlet	straight M12

Data sheet

Page 3/7

M12 Panel feed through adapters, X-coded, to RJ45 - straight

P/N

MWN811A415

EAN 4250184157441

2026/08/21

Version: O

Technical Data

Electrical characteristics

Current carrying capacity	0.5 A
Rated voltage	50 V AC / 60 V DC
Insulation resistance	min. 100 MOhm

Materials and material properties

Material - Housing	GD-Zn
Halogen free	yes
Material - Finish	Ni (nickel)
RoHS	compliant

Environmental conditions

Temperature (min. - max.)	
Temperature - Storage °C	-40 °C - 70 °C
Temperature - Storage °F	-40 °F - 158 °F
Temperature - Operating °C	-40 °C - 70 °C
Temperature - Operating °F	-40 °F - 158 °F
Particulate ingress interface 1	IP2X
Liquid ingress/immersion interface 1	IPX0
Particulate ingress interface 2	IP6X when plugged in
Liquid ingress/immersion interface 2	IPX5, IPX7 when plugged in
Overvoltage category	II
Degree of pollution	2

Approvals

UL listed (file no.)



DUXR.E178484



Data sheet

Page 4/7

M12 Panel feed through adapters, X-coded, to RJ45 - straight

P/N

MWN811A415

EAN 4250184157441

2026/08/21

Version: O

Technical Data

Standards/Regulations

Application-specific communications cabling systems

Profinet	yes
Connectors for electronic equipment	
circular connector	DIN EN 61076-2-109:2010-08
Rectangular connectors	IEC 60603-7-51
Railway applications	
Contact holder	Thermoplastic
Sealings	Elastomer
Shock and vibration	DIN EN 50155:2018-05, DIN EN 61373:2011-04 Class 1 Category B
Salt spray	DIN EN 50155:2018-05, (DIN EN 60068-2-11:2000-02/ 48h test KA)

Classifications

ETIM 7.0	EC001134
ETIM 8.0	EC001134
ETIM 9.0	EC001134
ETIM 10.0	EC001134

Packing details

Type of packaging	10 pc(s) / box
-------------------	----------------

Application note

This product is a standard product of METZ CONNECT. METZ CONNECT is not aware of the specific intended use of the goods by the Customer or any customers of the Customer. The Customer guarantees that it has fully and sufficiently tested the use of the goods and any product modifications, product changes or product enhancements with regard to the specific intended use in accordance with the state of the art or in any other way.



Data sheet

Page 5/7

M12 Panel feed through adapters, X-coded, to RJ45 - straight

P/N

MWN811A415

EAN 4250184157441

2026/08/21

Version: O

Accessories

P/N	Designation
700701	M12 screw plug for jacks IP54

Data sheet

Page 6/7

M12 Panel feed through adapters, X-coded, to RJ45 - straight

P/N

MWN811A415


EAN 4250184157441

2026/08/21


Version: O

Illustrations

Dimensional drawing



Drill pattern



Data sheet

Page 7/7

M12 Panel feed through adapters, X-coded, to RJ45 - straight

P/N

MWN811A415

EAN 4250184157441

2026/08/21

Version: O

Illustrations

Wiring diagram

