

Fuse switch disconnecter, 3p, NH00, AC23

Part no. PIFT0H331C155CCA
164000

General specifications		
Product name		Eaton Distribution parts
Part no.		PIFT0H331C155CCA
EAN		4015081605309
Product Length/Depth		590 millimetre
Product height		49.5 millimetre
Product width		280 millimetre
Product weight		5.15 kilogram
Compliances		RoHS conform
Product Tradename		None
Product Type		Distribution parts
Product Sub Type		None
Public Consumption		Yes
PDH Status		Active
Product Family Description		ES-PMCC-PDC-Eaton Distribution parts
Globally Marketable		Yes
Product Specification Details		
Actuator position		Front side
Actuator type		Long turning handle
Cable entry type		Side
Conditioned rated short-circuit current Iq		100 kA
Degree of protection (front side)		IP40
Electrical connection type of main circuit		Screw connection
Features		Motor drive optional
Fitted with:		Error protection Connectors
Number of poles		Three-pole
Power rating at AC-23, 400 V		0 kW
Rated conditional short-circuit current (Iq)		100 kA
Rated operating voltage (Ue) at AC - max		690 V
Rated operation power at AC-23, 400 V		0 kW
Rated operational power at AC-23A, 400 V, 50 Hz		0 kW
Rated permanent current (Iu)		160 A
Rated short-time withstand current (Icw)		0 kA
Rated uninterrupted current (Iu)		160 A
Suitable for		Front mounting
Suitable for fuses		NH00
With error protection		Yes

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Fuse switch disconnecter (EC001040)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse switch disconnecter (ec1@ss13-27-37-14-01 [AKF058018])		
Version as main switch		No
Version as safety switch		No
Max. rated operation voltage Ue AC	V	690
Rated permanent current Iu	A	160
Rated operation power at AC-23, 400 V	kW	0
Conditioned rated short-circuit current Iq	kA	100

Rated short-time withstand current Icw		kA	0
Suitable for fuses			NH00
Number of poles			3
With error protection			Yes
Type of electrical connection of main circuit			Screw connection
Cable entry			Side
Equipped with connectors			Yes
Suitable for floor mounting			No
Suitable for front mounting			Yes
Suitable for busbar mounting			No
Type of control element			Long turning handle
Position control element			Front side
Motor drive optional			Yes
Motor drive integrated			No
Version as emergency stop installation			No
Degree of protection (IP), front side			IP40