










SECTION B-B



SECTION C-C



- ## NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. RECOMMENDED MATING BLADE THICKNESS 0.6 ± 0.03 MM OR 0.64 ± 0.03 MM
RECOMMENDED MATING BLADE WIDTH NOT TO EXCEED 1.2 MM
AND NO LESS THAN 0.61 MM.

3. MAXIMUM CURRENT CAPACITY IS 10 AMPS WITH 0.8 MM² COPPER CABLE.

4. CRIMP DIMENSION FROM THE BACK OF THE CORE WING (INCLUDES THE FLARE OUT FROM THE CORE WING) TO THE END OF THE INSULATION WING.

- 2.05 MM MAX WIDTH, 2.1 MM MAX HEIGHT FOR CABLE SIZE UP TO 1.9 MM
2.35 MM MAX WIDTH, 2.40 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 1.8
2.67 MM MAX WIDTH, 2.67 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 2.2

5. * DENOTES DIMENSIONS MADE AT CUT-OFF & CRIMP DIE.

6. PLUS ANGLE IS WING BOTTOM SURFACE ROTATED COUNTERCLOCKWISE AGAINST THE BOX BOTTOM SURFACE.

3		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART D	
FROM	0		
TO	12	>12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
	±0.1	±0.2	
ANGULAR TOLERANCE ±2°			

	LINE DRAWN THROUGH A PART NUMBER	
	INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
	PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
	CONTACT APPLIC SALES TO ASSURE AVAILABILITY	
	END DATE	
	PART DRAWING	
	STYLE	
	VOLUME (CM)	DISTRICT CODE
		D
	UNLESS OTHERWISE SPECIFIED	
	THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-2018, PER THE UNIVERSAL DESIGN STANDARD BY 2017 FOR ISO 15011:2004 RECOGNITION REQUIREMENTS.	
	ALL DIMENSIONS ARE IN MILLIMETERS	
	REFERENCE	
2	TRIAL ANGLE PROJECTION	DO NOT SCALE
1		USE MATH DATA
		 NX

• APTIV •

CONNECTION SYSTEMS

WARREN, OH

COPYRIGHT 1979 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
 CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
 UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL
 AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
 PERMISSION OF APTIV, IS PROHIBITED.

DR	DATE
APW01	LUIS VILLARREAL
APW02	ROBERT B SNADER
APW03	ROBERT B SNADER
APW04	
APW05	

28FE19

01MR19

01MR19

SUBSTANCES OF CONCERN AND RECYCLED
 CONTENT PER APTIV 10949001

MATERIAL
 SEE CHART

DRAWING NAME:

TAXI TERM F OCS 1.2

DRAWING NUMBER

13543112

SIZE	SCALE
A0	10

FRAME	NO
1	OF 1

SHEET	NO
1	OF 1

STO	REV	NO	DATE