


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]				
	ENGLISH	METRIC	L ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
PMNF2-3F	--	M3	.78 [19,8]	.23 [5,9]	.20 [5,1]	.64 [16,3]	.13 [3,3]
PNF14-6FN*	#6	M3,5	.78 [19,8]	.24 [6,1]	.19 [4,8]	.64 [16,3]	.15 [3,8]
PNF14-6F	#6	M3,5	.78 [19,8]	.28 [7,1]	.22 [5,6]	.64 [16,3]	.15 [3,8]
PNF14-8F	#8	M4	.84 [21,3]	.31 [7,9]	.23 [5,8]	.68 [17,3]	.17 [4,3]
PNF14-10FN*	#10	--	.86 [21,8]	.31 [7,9]	.24 [6,1]	.70 [17,8]	.20 [5,1]
PNF14-10F	#10	--	.86 [21,8]	.34 [8,6]	.24 [6,1]	.70 [17,8]	.20 [5,1]
PMNF2-5F	--	M5	.86 [21,8]	.34 [8,6]	.25 [6,4]	.70 [17,8]	.20 [5,1]
PNF14-14F	1/4"	M6	1.03 [26,2]	.44 [11,2]	.32 [8,1]	.78 [19,8]	.27 [6,9]

* NOT UL LISTED OR CSA CERTIFIED

NOTES:

- USED FOR:
 - #16-14 AWG [1,5-2,5 mm²] SOLID OR STRANDED COPPER WIRE
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600 V. MAX. VOLTAGE RATING
- INSTALLATION TOOLS:
 - PRESSES: CP-871
 - APPLICATOR: CA-800EZ, CA9
 - DIE INSERTS: CD-800-2, CD9-2A
- WIRE STRIP LENGTH: 1/4" ^{+1/32} ₋₀ [6,4^{+0,8}]
- MATERIAL:
 - STAMPING: .03" [0,76] THK COPPER, TIN PLATED
 - HOUSING: NYLON, BLUE
 - SLEEVE: BRASS, TIN PLATED
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



CARRIER STRIP
(CONFIGURATION
MAY VARY)


.16 [4,1]
MAX. WIRE
INSUL. DIA.




LISTED
587H
E52164



CERTIFIED
LR31212



								TITLE FORK TERMINALS, 3 PC. NYLON (FUNNEL) INSULATED, #16-14				
								CUSTOMER DRAWING				
								ITEM REVISION NAME N41140BA/05		PANDUIT		
								DATASET FILE NAME N41140BA_DC/05A				
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .005 [.13] .XX ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION		MATERIAL: SEE NOTES		
05	09.10.12	JBN	LCA	VMB	ADDED METRIC EQUIVALENT. REVISED NOTES. UPDATED DRAWING TO CURRENT STANDARDS.	A41140		DRAWING NUMBER: A41140				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY GRM	DATE -	CHK FD	SCALE N.T.S.	SHT 1 OF 1	SIZE A