

NOTES:

1. MATERIALS AND FINISHES:
BODY - BRASS, NICKEL PLATING
REAR BODY - BeCu, NICKEL PLATING
CONTACT - BeCu, GOLD PLATING
INSULATOR - PTFE


2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 12 GHz
C. RETURN LOSS: -25 dB MIN @ DC - 6 GHz
-20 dB MIN @ 6 - 12 GHz
D. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS MIN.


3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -40°C TO +85°C

4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL, AD-BNCJMCXP-12G & DATE CODE"

THIRD ANGLE PROJ.

REVDESCRIPTIONDATEECNAPPR
ARELEASE TO MFG.24-Feb-2014261SV





CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1°	MATERIAL		DRAWN		DATE		TITLE		Amphenol RF www.amphenolrf.com	
	SEE NOTES		M.ZHANG		24-Feb-20					
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE		ENGINEER		DATE		BNC JACK TO MCX PLUG ADAPTER		DRAWING NO. AD-BNCJMCXP-12G	
	EAR# 9410		S.VO		25-Sep-19					
	REF: 31-70540-12G		APPROVED		DATE		SCALE: 10.0:1.0 SHEET 2 OF 2		ITEM NO. AD-BNCJMCXP-12G	
	CONFIGURATION LEVEL: In Work		S.HSIEH		27-Feb-20					
	FINISH		CAD FILE		DWG SIZE		REV		PART NO. AD-BNCJMCXP-12G	
				B		A				