




SL-156

TE Internal #: 3-770476-1

Tin (Sn), Socket Contact, 24 – 18 AWG, 250 VAC, .2 – .9 mm² Wire,
Locking Lance Contact Retention, Discrete Wire, Crimp, Phosphor
Bronze, SL-156

[View on TE.com >](#)

Connectors > Contacts > Connector Contacts > Connector Contacts: Wire-to-Board Socket, SL 156



Contact Type: **Socket**
Contact Mating Area Plating Material: **Tin (Sn)**
Wire Contact Termination Area Plating Material: **Tin**
Operating Voltage: **250 VAC**
Contact Retention Within Housing: **With**

[All Connector Contacts: Wire-to-Board Socket, SL 156 \(23\)](#)

Features

Product Type Features

Applied Pressure	High
------------------	------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Type	Socket
Contact Mating Area Plating Material	Tin (Sn)
Wire Contact Termination Area Plating Material	Tin
Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	10 A



Mating Square Post Dimension	1.14 mm[.045 in]
Contact Mating Area Plating Material Finish	Matte
Wire Contact Termination Area Plating Material Finish	Matte
Contact Underplating Material	Nickel

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
---------------------------------------	---------------

Dimensions

Wire Size	.2 – .9 mm²
Compatible Insulation Diameter Range	1.09 – 2.79 mm[.043 – .11 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Quantity	5500
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 2151033-1 OCEAN-2.0-APPLICATOR-S-070F100F-RSM	 TE Part # 91597-1 CCII SL-156 REC 24-18 ASSY	 TE Part # 7-2151033-7 OCEAN_2.0_SPARE_PART_KIT-070F100F
 TE Part # 90471-1 EXTRACTION TOOL, SC-156	 TE Part # 2151033-2 OCEAN-2.0-APPLICATOR-S-070F100FA-RSA	 TE Part # 58614-2 PROCRIMP, DIE, SL156	 TE Part # 58614-1 PROCRIMP, HT&D SL156

Also in the Series | SL-156

 Connector Contacts(23)	 Connector Hardware(4)	 Insertion & Extraction Tools(1)	 Power Contacts(13)
---	--	--	---



Rectangular Connector Housings(150)




Rectangular Power Connectors(147)



Wire-to-Board Connector Assemblies & Housings(146)


Customers Also Bought




TE Part #801068-SF
EV35-2.0-02-20M



TE Part #52957-3
TERMINAL,PG SPR SPD 16-14 10



TE Part #62057-3
250 FASTON FLAG REC 12-10 AWG TPBR



TE Part #63306-2
250 FASTON REC 18-14 AWG TPBR



TE Part #2-520183-2
ULTRA-FAST 250 ASY REC 22-18 TPBR




TE Part #521633-2
ULTRA-POD 250 ASY REC 18-14 AWG TPBR



TE Part #647344-7
07P SL156 HSG W/RP TB BLK #3



TE Part #CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156



TE Part #520935-9
PL&STANDARD FASTON 250 HOUSING REC BLA

Documents

Product Drawings
SL156 RECPT, SNNI/PHBZ

English

CAD Files
Customer View Model
ENG_CVM_3-770476-1_K.2d_dxf.zip

English

Customer View Model



[ENG_CVM_3-770476-1_K.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_3-770476-1_K.3d_igs.zip](#)

English

3D PDF

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_3-770476-1_Y.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-770476-1_Y.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-770476-1_Y.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[ENG_DS_82056_MTA_0818.pdf](#)

English

Product Specifications

Application Specification

English