



Part Number : [1300101748](#)

Product Description : Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), 16 AWG, Yellow TPE Cable, 0.60m (1.97') Length

Series Number : 130010

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : 115033K13M006

Documents & Resources

Drawings

[1300101748_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130010
Description	Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), 16 AWG, Yellow TPE Cable, 0.60m (1.97') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Double Ended
UPC	78172504646

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

Physical

Cable Diameter	12.70mm (.500")
Cable Length	0.61m (2.0')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	PVC

Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	148.000/g
Orientation	90° to 90°
Poles	5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	TPE
Wire Size (AWG)	16

This document was generated on Sep 14, 2025