



X7R - COMMERCIAL - 16Vdc to 10KVdc



Stable EIA Class II dielectric, with +/-15% temperature coefficient and predictable variation of electrical properties with time, temperature and voltage. These chips are designed for surface mount application with nickel barrier terminations suitable for solder wave, vapor phase or reflow solder board attachment. Also available in silver-palladium terminations for hybrid use with conductive epoxy. Class II X7R chips are used as decoupling, by-pass, filtering and transient voltage suppression elements.

CAPACITANCE & VOLTAGE SELECTION FOR POPULAR CHIP SIZES

3 digit code: two significant digits, followed by number of zeros eg: 183 = 18,000 pF. R denotes decimal, eg. 2R7 = 2.7 pF


MAX CAP & VOLTAGE

SIZE	0402	0504	0603	0805	1005	1206	1210	1515	1808		1812		1825						
Min Cap	121	121	121	121	121	121	121	151	151	151	151	151	471	471					
Tmax	.024	.044	.035	.054	.054	.064	.065	.130	.065	.080 ^x	.065	.100 ^x	.080	.140 ^x					
16V	562	393	273	124	154	334	474	125	684	824	125	155	185	225					
25V	472	333	223	104	124	274	474	105	564	564	105	125	155	225					
50V	472	333	223	104	124	274	474	824	394	564	824	125	155	225					
100V	472	333	223	683	823	184	334	684	274	394	564	824	125	185					
200V	222	153	103	333	473	104	184	564	184	224	334	564	824	155					
250V	152	103	682	273	393	683	124	394	124	154	224	394	684	125					
300V	•	•	•	153	183	473	823	274	823	104	154	224	474	824					
400V	•	•	•	123	123	273	563	224	563	823	104	184	334	564					
500V	•	•	•	123	822	223	563	154	563	683	104	154	334	474					
600V	•	•	•	822	822	183	393	124	393	563	683	124	224	394					
800V*	•	•	•	472	472	103	273	823	273	333	473	683	124	274					
1000V*	•	•	•	272	272	682	153	563	153	223	273	473	823	154					
1500V*	•	•	•	•	•	222	472	183	472	682	822	153	273	563					
2000V*	•	•	•	•	•	102	222	822	272	332	472	682	123	273					
3000V*	•	•	•	•	•	•	•	152	561	821	122	122	472	103					
4000V*	•	•	•	•	•	•	•	122	331	391	681	122	152	272					
5000V*	•	•	•	•	•	•	•	•	•	•	•	•	821	182					
6000V*	•	•	•	•	•	•	•	•	Note: “ x ” denotes a special thickness (see Tmax row above). An X is required in the part number. Please refer to page 10 for how to order.										
7000V*	•	•	•	•	•	•	•	•							•	•	•	•	•
8000V*	•	•	•	•	•	•	•	•							•	•	•	•	•
9000V*	•	•	•	•	•	•	•	•							•	•	•	•	•
10000V*	•	•	•	•	•	•	•	•							•	•	•	•	•

Note: "x" denotes a special thickness (see Tmax row above). An X is required in the part number. Please refer to page 10 for how to order.

* Units rated above 800V may require conformal coating in use to preclude arcing over the chip surface

NOTE: REFER TO PAGES 10 & 11 FOR ORDERING INFORMATION



See chart for standard EIA case sizes and available capacitance and voltage ratings. Special sizes, thicknesses and other voltage ratings are available, see other NOVACAP product offerings. High reliability testing is available refer to pages 22-23. Please consult the factory with your requirements. NOVACAP has complete testing facilities at your disposal.

CAPACITANCE & VOLTAGE SELECTION FOR POPULAR CHIP SIZES

3 digit code: two significant digits, followed by number of zeros eg: 183 = 18,000 pF. R denotes decimal, eg. 2R7 = 2.7 pF

MAX CAP & VOLTAGE

SIZE	2020	2221	2225	2520	3333	3530	4040	4540	5440	5550	6560	7565
Min Cap	102	471	471	471	102	102	102	102	102	102	222	222
Tmax	.180	.080	.080	.150 ^x	.180	.250	.250	.300	.300	.300	.300	.300
16V	185	155	225	275	Note: "x" denotes a special thickness (see Tmax row above). An X is required in the part number. Please refer to page 10 for how to order.					•	•	•
25V	155	125	185	225						•	•	•
50V	155	125	185	225						•	•	•
100V	155	125	155	225						•	•	•
200V	125	684	105	185	•	•	•	•	•	•	•	•
250V	105	564	824	155	•	•	•	•	•	•	•	•
300V	824	394	474	105	•	•	•	•	•	•	•	•
400V	564	274	394	684	•	•	•	•	•	•	•	•
500V	474	274	334	564	684	105	105	185	185	185	225	335
600V	274	224	274	474	394	684	684	155	155	155	225	275
800V*	224	124	154	334	274	474	394	684	824	105	155	225
1000V*	154	823	104	224	184	334	334	564	684	684	105	155
1500V*	473	273	333	683	563	124	124	274	334	334	474	684
2000V*	273	123	153	333	273	823	683	154	184	184	274	394
3000V*	103	472	562	123	123	333	273	683	683	823	124	184
4000V*	272	152	152	332	472	183	153	223	333	393	473	823
5000V*	152	821	102	222	272	123	103	123	183	223	333	473
6000V*	•	•	•	•	•	682	562	822	123	153	223	333
7000V*	•	•	•	•	•	•	472	562	822	103	153	223
8000V*	•	•	•	•	•	•	332	472	682	822	123	153
9000V*	•	•	•	•	•	•	272	332	472	562	103	123
10000V*	•	•	•	•	•	•	182	272	392	472	682	103

* Units rated above 800V may require conformal coating in use to preclude arcing over the chip surface

NOTE: REFER TO PAGES 10 & 11 FOR ORDERING INFORMATION



STANDARD SMT CHIP P/N BREAKDOWN

I 206 N 472 J 101 N X050 H T M - HB

Case Size

Dielectric Code

Code	EIA	Class
N	COG/NP0	Ultra Stable
B	X7R	Stable
X	BX	MIL
Y	Y5V	General Purpose
Z	Z5U	General Purpose
S	X8R	High Temp up to 150°C
D	COG/NPO	High Temp up to 200°C
E	Class II (Stable)	High Temp up to 200°C
F	160°	High Temp up to 160°C
G	160°	High Temp up to 160°C
W	X5R	Stable
P	85°	Pulse Power
R	200°	Pulse Energy

Capacitance

1st two digits are significant, third digit denotes number of zeros, R= decimal

Examples:

1R0 = 1.0 pF 273 = .027 μ F
 120 = 12 pF 474 = 0.47 μ F
 471 = 470 pF 105 = 1.0 μ F
 102 = 1,000 pF

Capacitance Tolerance

Code		COG NPO	X7R	BX	Z5U Y5V	X8R 150°C	D/F	E/G	W X5R
Cap Value < 10pF									
B	± 0.10 pF								
C	± 0.25 pF								
D	± 0.50 pF								
F	$\pm 1\%$								
G	$\pm 2\%$								
J	$\pm 5\%$								
K	$\pm 10\%$								
M	$\pm 20\%$								
Z	+80% -20%								
P	+100%/-0%								

Marking

M = Marked
 None = Unmarked
 Marking not available on sizes 0603 and below

Packaging

T = Tape and Reel
 W = Waffle Pack
 None = Bulk

High Reliability Testing

H = High Reliability Testing Required
 None = Standard SMT, no High-Rel
 HB = MIL-PRF-55681 Group A
 HK = MIL-PRF-38534 Class K
 HS = MIL-PRF-123 Group A

Special Thickness

X in the part number denotes a special thickness other than standard. Specify in mils if required. (As shown above X=.050")
 If no X in the part number then thickness is standard per Novacap catalog specifications.


Termination

N = Nickel Barrier (100% Tin) (RoHS)
 P = Palladium Silver
 PR = Palladium Silver (RoHS)
 Y = Nickel Barrier (90%Tin/10%Lead)
 S = Silver
 C = Polymer with Nickel Barrier (100% Tin) (RoHS)
 D = Polymer with Nickel Barrier (90%Tin/10%Lead)
 V = Non-Solderable Silver (RoHS)
 NG = Nickel Gold

Voltage


Examples:
 160 = 16 Volts 102 = 1000 Volts
 101 = 100 Volts 502 = 5000 Volts
 501 = 500 Volts 103 = 10,000 Volts

This ordering information relates to NOVACAP's standard surface mount capacitors. Please refer to the specific catalog pages for ordering information for our application specific products; ie: Stacked, Leaded, Capacitor Arrays, Pulsed Power capacitors and other specialty products.



PART NUMBER PREFIX DEFINITIONS

LS = Y3 Certified Safety Capacitor	pg. 38
ES = Y2 Certified Safety Capacitor	pg. 39
AP = Arc Prevention Capacitor	pg. 54
CR = Cap-Rack Capacitor Array	pg. 42 - 43
RC = Bleed Resistor	pg. 34 - 37
RD = Ring Detect Capacitor	pg. 40
ST = Stacked Capacitor Assembly	pg. 54 - 55
SM = Hi-Rel Stacked Capacitor Assembly	pg. 54 - 55



CODE COMBINATIONS

Dielectric Code	Max. Temp. Rated	Terminations (allowed)
N (COG/NPO)	125°	N, P, Y, S, V, NG, PR
B (X7R)	125°	N, P, Y, C, D, S, V, NG, PR
X (BX)	125°	N, P, Y, C, D, S, V, NG, PR
Y (Y5V)	85°	N, Y, C, D
Z (Z5U)	85°	N, Y, C, D
D (NPO-HIGH TEMP)	200°	P, S, V, PR
E (CLASS II-HIGH TEMP)	200°	P, S, V, PR
F (NPO-HIGH TEMP)	160°	N, P, Y, S, V, C, D, PR
G (CLASS II-HIGH TEMP)	160°	N, P, Y, S, V, C, D, PR
S (X8R)	150°	N, P, Y, S, V, C, D, PR
P (PULSE POWER)	85°	P, PR
R (R2D)	200°	P, PR
W (X5R)	85°	N, Y, NG

DIMENSIONS
INCHES (MM)

SIZE	0402	0504	0603	0805	0907	1005	1206	1210	1515	1808	1812	1825
LENGTH L	.040 (1.02)	.050 (1.27)	.060 (1.52)	.080 (2.03)	.090 (2.29)	.100 (2.54)	.125 (3.18)	.125 (3.18)	.150 (3.81)	.180 (4.57)	.180 (4.57)	.180 (4.57)
WIDTH W	.020 (.508)	.040 (1.02)	.030 (.762)	.050 (1.27)	.070 (1.78)	.050 (1.27)	.060 (1.52)	.100 (2.54)	.150 (3.81)	.080 (2.03)	.125 (3.18)	.250 (6.35)
T MAX.	.024 (.610)	.044 (1.12)	.035 (.889)	.054 (1.37)	.054 (1.37)	.054 (1.37)	.064 (1.63)	.065 (1.65)	.130 (3.30)	.065 (1.65)	.065 (1.65)	.080 (2.03)
MB	.010 (.254)	.014 (.356)	.014 (.356)	.020 (.508)	.020 (.508)	.020 (.508)	.020 (.508)	.020 (.508)	.030 (.762)	.024 (.610)	.024 (.610)	.024 (.610)
LENGTH	.004 (.102)	.006 (.152)	.006 (.152)	.008 (.203)	.008 (.203)	.008 (.203)	.008 (.203)	.008 (.203)	.015 (.381)	.012 (.305)	.012 (.305)	.012 (.305)
WIDTH	.004 (.102)	.006 (.152)	.006 (.152)	.008 (.203)	.008 (.203)	.008 (.203)	.008 (.203)	.008 (.203)	.015 (.381)	.008 (.203)	.008 (.203)	.015 (.381)
MB	.006 (.152)	.006 (.152)	.006 (.152)	.010 (.254)	.010 (.254)	.010 (.254)	.010 (.254)	.010 (.254)	.015 (.381)	.014 (.356)	.014 (.356)	.014 (.356)

DIMENSIONS
INCHES (MM)

SIZE	2020	2221	2225	2520	3333	3530	4040	4540	5440	5550	6560	7565
LENGTH L	.200 (5.08)	.220 (5.59)	.220 (5.59)	.250 (6.35)	.330 (8.38)	.350 (8.89)	.400 (10.2)	.450 (11.4)	.540 (13.7)	.550 (14.0)	.650 (16.5)	.750 (19.1)
WIDTH W	.200 (5.08)	.210 (5.33)	.250 (6.35)	.200 (5.08)	.330 (8.38)	.300 (7.62)	.400 (10.2)	.400 (10.2)	.400 (10.2)	.500 (12.7)	.600 (15.2)	.650 (16.5)
T MAX.	.180 (4.57)	.080 (2.03)	.080 (2.03)	.180 (4.57)	.250 (6.35)	.250 (6.35)	.300 (7.62)	.300 (7.62)	.300 (7.62)	.300 (7.62)	.300 (7.62)	.300 (7.62)
MB	.024 (.610)	.030 (.762)	.030 (.762)	.030 (.762)	.030 (.762)	.030 (.762)	.040 (1.02)	.040 (1.02)	.040 (1.02)	.040 (1.02)	.040 (1.02)	.040 (1.02)
LENGTH	.015 (.381)	.015 (.381)	.015 (.381)	.015 (.381)	.017 (.432)	.018 (.457)	.020 (.508)	.023 (.584)	.027 (.686)	.028 (.711)	.033 (.838)	.038 (.965)
WIDTH	.015 (.381)	.015 (.381)	.015 (.381)	.015 (.381)	.017 (.432)	.015 (.381)	.020 (.508)	.020 (.508)	.020 (.508)	.025 (.635)	.030 (.762)	.033 (.838)
MB	.014 (.356)	.015 (.381)	.015 (.381)	.015 (.381)	.015 (.381)	.015 (.381)	.020 (.508)	.020 (.508)	.020 (.508)	.020 (.508)	.020 (.508)	.020 (.508)