

# Features

## Regulated Converter

- High output voltage DIP24 converter
- Adjustable output voltage up to 200VDC
- Cascadable for output voltages up to 400VDC
- 3kVDC input/output isolation
- Remote voltage programming by external voltage or resistance
- Continuous short circuit protection
- Ambient temperature up to +85°C

## Description

The Rxx-B series are 5W regulated high output voltage isolated DC/DC converters in a DIP24 package. Three adjustable output voltages of 87V (41-120V), 103V (50-135V) or 159V (92-200V) are offered, with nominal input voltage options of 5V, 12V, 15V or 24V. The modules can be cascaded for higher output voltages up to 400VDC. The output is isolated from the input with 3kVDC isolation and the modules can be operated over a -40°C to +85°C ambient temperature range. The Rxx-B series is safety certified with IEC/EN60950-1 certifications (the R24-100B has additionally UL/IEC/EN62368 with CB Report). A three year warranty is offered.

## Selection Guide

| Part Number | Input Voltage Range [VDC] | nom. Output Voltage [VDC] | Output Voltage Range [VDC] | Output Power max. <sup>(1)</sup> [W] | Efficiency typ. <sup>(2)</sup> [%] | Max. Capacitive Load <sup>(3)</sup> [μF] |
|-------------|---------------------------|---------------------------|----------------------------|--------------------------------------|------------------------------------|------------------------------------------|
| R05-100B    | 4.5 - 6                   | 87                        | +41...+120                 | 3                                    | 77                                 | 20                                       |
| R12-100B    | 10 - 14                   | 103                       | +50...+135                 | 5                                    | 82                                 | 30                                       |
| R15-100B    | 14 - 17                   | 103                       | +59...+130                 | 5                                    | 82                                 | 30                                       |
| R24-100B    | 21 - 27                   | 105                       | +56...+135                 | 5                                    | 84                                 | 30                                       |
| R12-150B    | 10 - 14                   | 159                       | +92...+200                 | 5                                    | 82                                 | 40                                       |
| R15-150B    | 14 - 17                   | 159                       | +92...+200                 | 5                                    | 82                                 | 40                                       |
| R24-150B    | 21 - 27                   | 159                       | +92...+200                 | 5                                    | 84                                 | 40                                       |

### Notes:

Note1: Refer to „**Power Limit**“ graph

Note2: Efficiency is tested at nominal input and full load at +25°C ambient

Note3: Max. Cap Load is tested at nominal input and full resistive load.

If the load is mainly capacitive, it should have a minimum resistive load of 10mA


## Model Numbering

nom. Input Voltage **R** - **B** Output Voltage

**RECOM**  
DC/DC Converter

**Rxx-B**

**5 Watt  
DIP24  
Single Output**




EN60950-1 certified  
IEC60950-1 certified

**Specifications** (measured @ Ta= 25°C, nom. Vin and full load)


**BASIC CHARACTERISTICS**

| Parameter                    | Condition                | Min.                                    | Typ.    | Max.     |
|------------------------------|--------------------------|-----------------------------------------|---------|----------|
| Input Voltage Range          | nom. Vin= 5VDC           | 4.5VDC                                  | 5VDC    | 6VDC     |
|                              | nom. Vin= 12VDC          | 10VDC                                   | 12VDC   | 14VDC    |
|                              | nom. Vin= 15VDC          | 14VDC                                   | 15VDC   | 17VDC    |
|                              | nom. Vin= 24VDC          | 21VDC                                   | 24VDC   | 27VDC    |
| Output Current               | refer to „Power Limit“   |                                         |         | 50mA     |
| Output Power                 | 5V                       |                                         |         | 3W       |
|                              | all others               |                                         |         | 5W       |
| Output Voltage Adjust        | External Voltage         | 0VDC                                    |         | 4VDC     |
|                              | External Resistor        | 0kΩ                                     |         | 5kΩ      |
| Internal Voltage Reference   | refer to page I-4 to I-5 | regulated 5VDC with 1kΩ series resistor |         |          |
| Internal Operating Frequency |                          |                                         | 200kHz  |          |
| Output Ripple and Noise      | 20MHz BW                 |                                         | 60mVp-p | 100mVp-p |

**Efficiency vs. Output Voltage**




**Output Ripple vs. Output Voltage**



**Power Limit**

**R12-150B; R15-150B; R24-150**




continued on next page


**Specifications** (measured @ Ta= 25°C, nom. Vin and full load)

**Power Limit**


**R05-100B**




**R12-100B**



**R15-100B**



**R24-100B**



**REGULATIONS**

| Parameter       | Condition             | Value      |
|-----------------|-----------------------|------------|
| Output Accuracy |                       | ±5.0% max. |
| Line Regulation | low line to high line | ±0.5% max. |
| Load Regulation | 20% to 100% load      | 0.5% max.  |

**PROTECTIONS**

| Parameter                      | Condition           | Value                         |
|--------------------------------|---------------------|-------------------------------|
| Short Circuit Protection (SCP) |                     | continuous, automatic restart |
| Isolation Voltage              | tested for 1 second | 3kVDC min.                    |
| Isolation Resistance           |                     | 1GΩ min.                      |
| Isolation Capacitance          |                     | 20pF typ.                     |


### Specifications (measured @ Ta= 25°C, nom. Vin and full load)

#### ENVIRONMENTAL

| Parameter                   | Condition                                       |       | Value                        |
|-----------------------------|-------------------------------------------------|-------|------------------------------|
| Operating Temperature Range | with derating @ free air convection (see graph) |       | -40°C to +85°C               |
|                             | full load @ free air convection (see graph)     |       | -40°C to +70°C               |
| Temperature Coefficient     |                                                 |       | ± 0.02%/K                    |
| Operating Altitude          |                                                 |       | 2000m                        |
| Operating Humidity          | non-condensing                                  |       | 95% RH max.                  |
| Pollution Degree            |                                                 |       | PD2                          |
| MTBF                        | according to MIL-HDBK-217F, G.B.                | +25°C | 1400 x 10 <sup>3</sup> hours |

#### Derating Graph

(@ free air convection)



#### SAFETY AND CERTIFICATIONS

| Certificate Type (Safety)                                         | Report / File Number | Standard                                                               |
|-------------------------------------------------------------------|----------------------|------------------------------------------------------------------------|
| Information Technology Equipment, General Requirements for Safety | SPCLVD1605077-02     | IEC60950-1:2005, 2nd Edition + AM 2:2013<br>EN60950-1:2006 + AM 2:2013 |
| EAC                                                               | RU-AT.49.09571       | TP TC 004/2011                                                         |
| RoHS2+                                                            |                      | RoHS-2001/65/EU + AM-2015/863                                          |


#### DIMENSION AND PHYSICAL CHARACTERISTICS

| Parameter                 | Type    | Value                                    |
|---------------------------|---------|------------------------------------------|
| Material                  | case    | non conductive black plastic, (UL94 V-0) |
|                           | potting | epoxy, (UL94 V-0)                        |
|                           | PCB     | FR4, (UL94 V-0)                          |
| Package Dimension (LxWxH) |         | 31.2 x 20.3 x 9.4mm                      |
| Package Weight            |         | 12g typ.                                 |

continued on next page

Specifications (measured @ Ta= 25°C, nom. Vin and full load)

### Dimension Drawing (mm)





### Pin Connections

| Pin # | Single |
|-------|--------|
| 2,3   | -Vin   |
| 8,17  | Vadj.  |
| 9,16  | V ref  |
| 10,15 | -Vout  |
| 12,13 | +Vout  |
| 22,23 | +Vin   |

Tolerance: xx.x= ±0.5mm  
xx.xx= ±0.25mm

### INSTALLATION AND APPLICATION

#### Output Voltage Adjust





#### Notes:

- Note3: 0Ω means Vadj connected to COM; no connection to Vref  
Note4: 0Ω means Vadj connected to Vref; no connection to COM


continued on next page

Specifications (measured @ Ta= 25°C, nom. Vin and full load)

For Remote Voltage Control



Cascade Circuit



Cascade Combinations

| U1       | U2       | Vout Range |
|----------|----------|------------|
| R05-100B | R05-100B | 160~240    |
| Rxx-100B | Rxx-100B | 190~260    |
| Rxx-150B | Rxx-100B | 230~330    |
| Rxx-150B | Rxx-150B | 305~400    |

xx = 12, 15 or 24

Note: When cascaded, only one Rxx-B may be adjustable, the other must be fixed voltage.

PACKAGING INFORMATION

| Parameter                   | Type | Value                 |
|-----------------------------|------|-----------------------|
| Packaging Dimension (LxWxH) | tube | 530.0 x 23.0 x 19.0mm |
| Packaging Quantity          | tube | 6pcs                  |
| Storage Temperature Range   |      | - 50°C to +125°C      |
| Storage Humidity            |      | 95% RH max.           |

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.