

MODEL NUMBER	"A"	INTERFACE PER	SH
CBBJ79	9/16	MIL-STD-348 FIG. 201-2	1
CBBJ79S	5/8 w/3X Ø.047 SAFETY WIRE HOLES		
CBBJ79TL	9/16		
CBBJ79TLS	5/8 w/3X Ø.047 SAFETY WIRE HOLES		
CBBJ79FL	9/16		
CBBJ79FLS	5/8 w/3X Ø.047 SAFETY WIRE HOLES		
CBBJ379	9/16	MIL-STD-348 FIG. 202-2	
CBBJ379S	5/8 w/3X Ø.047 SAFETY WIRE HOLES		
CBBJ79TL-1M	9/16	MIL-STD-348 FIG. 201-2	2
CBBJ79TL-1M			
CBBJ379-1M	9/16	MIL-STD-348 FIG. 202-2	


REV	ECO	DATE
E	57271	6/14/2019
F	57982	6/15/2021
G	60000	2/6/2025




CBBJ79S SHOWN



RECOMMENDED MTG HOLE PATTERN



RECOMMENDED PANEL CUTOUT



CBBJ79 SHOWN

CBBJ79TL SHOWN

CBBJ79FL SHOWN

CBBJ379 SHOWN

NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:
   1.1 BODY: TIN PLATED BRASS
   1.2 INSULATOR & DIELECTRIC: PTFE (TEFLON)
   1.3 INTERMEDIATE CONTACT: GOLD PLATED BRASS
   1.4 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
   1.5 GASKET: SILICONE RUBBER
   1.6 MOUNTING HARDWARE: GOLD PLATED COPPER ALLOY

2. ELECTRICAL:
   2.1 FREQUENCY (MAX): 500 MHz
   2.2 IMPEDANCE: NON-CONSTANT

3. PANEL NUT TORQUE (MAX): 35 INCH POUNDS

4. PANEL THICKNESS (MAX): .109

NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.

INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018

Model No: CBBJX79YYZ-AA

RoHS2 ☑ 2015/863/EU

Cage Code 14949

3RD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED UNITS: INCH
.XX ±.02
.XXX ±.010
ANGLES ±2°

ENGINEER: C.MONAHAN

Date: 2/6/2025

TROMPETER

Title: TRB/TRT BULKHEAD CIRCUIT BOARD JACK

Drawing No. 3-0272 REV. G


Size A | DO NOT SCALE DRAWING | Workmanship Std: TFS-4 | Sheet 1 OF 2

Downloaded from Arrow.com.

Please read our datasheet & drawing disclaimer here.

MODEL NUMBER	SH
CBBJ79	1
CBBJ79S	
CBBJ79TL	
CBBJ79TLS	
CBBJ79FL	
CBBJ79FLS	
CBBJ379	
CBBJ379S	
CBBJ79-1M	2
CBBJ79TL-1M	
CBBJ379-1M	

REV	ECO	DATE
E	57271	6/14/2019
F	57982	6/15/2021
G	60000	2/6/2025



CBBJ379-1M SHOWN

NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:
 1.1 CBBJ79TL-1M & CBBJ379-1M:
  1.1.1 BODY: SILVER PLATED BRASS
  1.1.2 INSULATOR & DIELECTRIC: PTFE (TEFLON)
  1.1.3 INTERMEDIATE CONTACT: GOLD PLATED BRASS
  1.1.4 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
  1.1.5 GASKET: SILICONE RUBBER
  1.1.6 MOUNTING HARDWARE: SILVER PLATED COPPER ALLOY

NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.

INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018

Model No: CBBJX79YYZ-AA

RoHS2 ☑ 2015/863/EU

Cage Code 14949

3RD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED UNITS: INCH
.XX ±.02
.XXX ±.010
ANGLES ±2°

ENGINEER: C.MONAHAN

Date: 2/6/2025

TROMPETER

Title: TRB/TRT BULKHEAD CIRCUIT BOARD JACK

Drawing No. 3-0272

REV. G

Size A | DO NOT SCALE DRAWING | Workmanship Std: TFS-4 | Sheet 2 OF 2

Downloaded from Arrow.com.