




8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

REVISONS

AD

25

PR	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

1

HOUSING MATERIAL: THERMOPLASTIC, COLOR—NATURAL

2

CONTACT MATERIAL: COPPER ALLOY.

3

CONTACT FINISH: .00127—.00254 [.000050—.000100] NICKEL UNDERPLATE ALL OVER; .00076 [.000030] GOLD PLATE IN CONTACT AREA, TIN—LEAD PLATED SOLDER TAILS, NO LUBRICANT.

4

SOLDER TAILS MUST FIT HOLE PATTERN AS SHOWN ON THE RECOMMENDED P.C. BOARD LAYOUT.

5

DIMENSIONS IN BRACKETS ARE IN INCHES.

6

HOUSINGS WITH CENTER MOUNTING IS RECOMMENDED FOR ASSEMBLIES HAVING 75 CONTACTS PER ROW OR MORE.

137.16 [5.400]	54	140.31 [5.524]	151.13 [5.950]	158.75 [6.250]	165	598213—8
99.06 [3.900]	39	102.21 [4.024]	113.03 [4.450]	120.65 [4.750]	120	598213—5
E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.


DWN
KIRAN HOLAL
CHK
ALEXANDER SHARPE
APVD
ALEXANDER SHARPE

13JUN2013
13JUN2013
13JUN2013

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

± —
± —
± —
± 0.13 [.005]
± — ± —



FINISH

3

MATERIAL

1

2

TE Connectivity

NAME

HDI, 3 ROW, RECEPTACLE ASSEMBLY,
4.57 [.180] LONG SOLDER TAILS,
.00076 [.000030] GOLD PLATE, NO LUBRICANT

PRODUCT SPEC

APPLICATION SPEC

SIZE
A1

CAGE CODE
00779

DRAWING NO
598213

RESTRICTED TO

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
A

4805 (3/11)

Downloaded from [Arrow.com](#)