

TO-220



ITO-220



TO-263 (D²PAK)



Pin Definition:

1. Ground
2. Input (tab)
3. Output

General Description

The TS7900A series of fixed output negative voltage regulators are intended as complements to the popular TS7800A series device. These negative regulators are available in the same seven-voltage options as the TS7900A devices. In addition, one extra voltage option commonly employed in MECL systems is also available in the negative TS7900A Series. Available in fixed output voltage options from -5.0 to -24 volts, these regulators employ current limiting, thermal shutdown, and safe-area compensation--making them remarkably rugged under most operating conditions. With adequate heat sinking they can deliver output currents in excess of 1 ampere. This series is offered in 3-pin TO-220, ITO-220 & TO-263 package.

Features


- Output Voltage Range -5 to -24V
- Output current up to 1A
- No external components required
- Internal thermal overload protection
- Internal short-circuit current limiting
- Output transistor safe-area compensation
- Output voltage offered in 2% tolerance

Ordering Information

Part No.	Package	Packing
TS79xxACZ C0	TO-220	50pcs / Tube
TS79xxACI C0	ITO-220	50pcs / Tube
TS79xxACM RN	TO-263	800pcs / 13" Reel

Note: Where **xx** denote voltage option

Standard Application Circuit



A common ground is required between the input and the output voltages. The input voltage must remain typically 2.0V above the output voltage even during the low point on the Input ripple voltage.

XX = these two digits of the type number indicate voltage.

* = C_{in} is required if regulator is located an appreciable distance from power supply filter.

** = C_o is not needed for stability; however, it does improve transient response.

Absolute Maximum Rating (Ta = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Input Voltage	V _{IN} *	-35	V
Input Voltage	V _{IN} **	-40	V
Power Dissipation	P _D	Internal Limited	W
Operating Junction Temperature	T _J	0~+125	°C
Storage Temperature Range	T _{STG}	-65~+150	°C

Note: * TS7905A to TS7918A

** TS7924A

*** Follow the derating curve

TS7900A Series

3-Terminal Fixed Negative Voltage Regulator

TS7905A Electrical Characteristics

($V_{in} = -10V$, $I_{out} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Output voltage	V_{out}	$T_j = 25^{\circ}C$	-4.90	-5	-5.10	V
		$-7.5V \leq V_{in} \leq -20V$, $10mA \leq I_{out} \leq 1A$, $PD \leq 15W$	-4.85	-5	-5.15	
Line Regulation	REG _{line}	$T_j = 25^{\circ}C$				mV
		$-7.5V \leq V_{in} \leq -25V$	--	3	100	
		$-8V \leq V_{in} \leq -12V$	--	1	50	
Load Regulation	REG _{load}	$T_j = 25^{\circ}C$				
		$10mA \leq I_{out} \leq 1A$	--	15	100	
		$250mA \leq I_{out} \leq 750mA$	--	5	50	
Quiescent Current	I_q	$I_{out} = 0$, $T_j = 25^{\circ}C$	--	4	8	mA
Quiescent Current Change	ΔI_q	$-7.5V \leq V_{in} \leq -25V$	--	--	1.3	
		$10mA \leq I_{out} \leq 1A$	--	--	0.5	
Output Noise Voltage	V_n	$10Hz \leq f \leq 100KHz$, $T_j = 25^{\circ}C$	--	40	--	μV
Ripple Rejection Ratio	RR	$f = 120Hz$, $-8V \leq V_{in} \leq -18V$	62	74	--	dB
Voltage Drop	V_{drop}	$I_{out} = 1.0A$, $T_j = 25^{\circ}C$	--	2	--	V
Output Short Circuit Current	I_{os}	$T_j = 25^{\circ}C$	--	750	--	mA
Peak Output Current	$I_{o peak}$	$T_j = 25^{\circ}C$	--	2.1	--	A
Temperature Coefficient of Output Voltage	$\Delta V_{out} / \Delta T_j$	$I_{out} = 10mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$	--	-0.1	--	mV/ $^{\circ}C$

TS7906A Electrical Characteristics

($V_{in} = -11V$, $I_{out} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Output Voltage	V_{out}	$T_j = 25^{\circ}C$	-5.88	-6	-6.12	V
		$-8.5V \leq V_{in} \leq -21V$, $10mA \leq I_{out} \leq 1A$, $PD \leq 15W$	-5.76	-6	-6.24	
Line Regulation	REG _{line}	$T_j = 25^{\circ}C$				mV
		$-8.5V \leq V_{in} \leq -25V$	--	5	120	
		$-9V \leq V_{in} \leq -13V$	--	1.5	60	
Load Regulation	REG _{load}	$T_j = 25^{\circ}C$				
		$10mA \leq I_{out} \leq 1A$	--	14	120	
		$250mA \leq I_{out} \leq 750mA$	--	4	60	
Quiescent Current	I_q	$I_{out} = 0$, $T_j = 25^{\circ}C$	--	4	8	mA
Quiescent Current Change	ΔI_q	$-8.5V \leq V_{in} \leq -25V$	--	--	1.3	
		$10mA \leq I_{out} \leq 1A$	--	--	0.5	
Output Noise Voltage	V_n	$10Hz \leq f \leq 100KHz$, $T_j = 25^{\circ}C$	--	44	--	μV
Ripple Rejection Ratio	RR	$f = 120Hz$, $-9V \leq V_{in} \leq -19V$	60	73	--	dB
Voltage Drop	V_{drop}	$I_{out} = 1.0A$, $T_j = 25^{\circ}C$	--	2	--	V
Output Short Circuit Current	I_{os}	$T_j = 25^{\circ}C$	--	550	--	mA
Peak Output Current	$I_{o peak}$	$T_j = 25^{\circ}C$	--	2.1	--	A
Temperature Coefficient of Output Voltage	$\Delta V_{out} / \Delta T_j$	$I_{out} = 10mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$	--	-0.1	--	mV/ $^{\circ}C$

- Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible, and thermal effects must be taken into account separately.
- This specification applies only for DC power dissipation permitted by absolute maximum ratings.

TS7900A Series

3-Terminal Fixed Negative Voltage Regulator

TS7908A Electrical Characteristics

$V_{in} = -14V$, $I_{out} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Output voltage	V_{out}	$T_j = 25^{\circ}C$	-7.84	-8	-8.16	V
		$-10.5V \leq V_{in} \leq -23V$, $10mA \leq I_{out} \leq 1A$, $PD \leq 15W$	-7.68	-8	-8.32	
Line Regulation	REGLine	$T_j = 25^{\circ}C$				mV
		$-10.5V \leq V_{in} \leq -25V$	--	6	160	
Load Regulation	REGload	$T_j = 25^{\circ}C$				
		$10mA \leq I_{out} \leq 1A$	--	12	160	
Quiescent Current	I_q	$I_{out} = 0$, $T_j = 25^{\circ}C$	--	4.3	8	mA
Quiescent Current Change	ΔI_q	$10.5V \leq V_{in} \leq 25V$	--	--	1	
		$10mA \leq I_{out} \leq 1A$	--	--	0.5	
Output Noise Voltage	V_n	$10Hz \leq f \leq 100KHz$, $T_j = 25^{\circ}C$	--	52	--	μV
Ripple Rejection Ratio	RR	$f = 120Hz$, $11V \leq V_{in} \leq 21V$	56	72	--	dB
Voltage Drop	V_{drop}	$I_{out} = 1.0A$, $T_j = 25^{\circ}C$	--	2	--	V
Output Short Circuit Current	I_{os}	$T_j = 25^{\circ}C$	--	450	--	mA
Peak Output Current	$I_{o peak}$	$T_j = 25^{\circ}C$	--	2.1	--	A
Temperature Coefficient of Output Voltage	$\Delta V_{out} / \Delta T_j$	$I_{out} = 10mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$	--	-1	--	mV/ $^{\circ}C$

TS7909A Electrical Characteristics

($V_{in} = -15V$, $I_{out} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Output Voltage	V_{out}	$T_j = 25^{\circ}C$	-8.82	-9	-9.18	V
		$-11.5V \leq V_{in} \leq -23V$, $10mA \leq I_{out} \leq 1A$, $PD \leq 15W$	-8.64	-9	-9.36	
Line Regulation	REGLine	$T_j = 25^{\circ}C$				mV
		$-11.5V \leq V_{in} \leq -26V$	--	6	180	
Load Regulation	REGload	$T_j = 25^{\circ}C$				
		$10mA \leq I_{out} \leq 1A$	--	12	180	
Quiescent Current	I_q	$I_{out} = 0$, $T_j = 25^{\circ}C$	--	4.3	8	mA
Quiescent Current Change	ΔI_q	$-11.5V \leq V_{in} \leq -26V$	--	--	1	
		$10mA \leq I_{out} \leq 1A$	--	--	0.5	
Output Noise Voltage	V_n	$10Hz \leq f \leq 100KHz$, $T_j = 25^{\circ}C$	--	58	--	μV
Ripple Rejection Ratio	RR	$f = 120Hz$, $-12V \leq V_{in} \leq -22V$	56	71	--	dB
Voltage Drop	V_{drop}	$I_{out} = 1.0A$, $T_j = 25^{\circ}C$	--	2	--	V
Output Short Circuit Current	I_{os}	$T_j = 25^{\circ}C$	--	450	--	mA
Peak Output Current	$I_{o peak}$	$T_j = 25^{\circ}C$	--	2.1	--	A
Temperature Coefficient of Output Voltage	$\Delta V_{out} / \Delta T_j$	$I_{out} = 10mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$	--	-1	--	mV/ $^{\circ}C$

- Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible, and thermal effects must be taken into account separately.
- This specification applies only for DC power dissipation permitted by absolute maximum ratings.

TS7900A Series

3-Terminal Fixed Negative Voltage Regulator

TS7912A Electrical Characteristics

($V_{in} = -19V$, $I_{out} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Output Voltage	V_{out}	$T_j = 25^{\circ}C$	-11.76	-12	-12.24	V
		$-14.5V \leq V_{in} \leq -27V$, $10mA \leq I_{out} \leq 1A$, $PD \leq 15W$	-11.52	-12	-12.48	
Line Regulation	REG _{line}	$T_j = 25^{\circ}C$				mV
		$-14.5V \leq V_{in} \leq -30V$	--	10	240	
		$-15V \leq V_{in} \leq -19V$	--	3	120	
		$10mA \leq I_{out} \leq 1A$	--	12	240	
Load Regulation	REG _{load}	$T_j = 25^{\circ}C$				
		$250mA \leq I_{out} \leq 750mA$	--	4	120	
Quiescent Current	I_q	$T_j = 25^{\circ}C$, $I_{out} = 0$	--	4.3	8	mA
Quiescent Current Change	ΔI_q	$-14.5V \leq V_{in} \leq -30V$	--	--	1	
		$10mA \leq I_{out} \leq 1A$	--	--	0.5	
Output Noise Voltage	V_n	$10Hz \leq f \leq 100KHz$, $T_j = 25^{\circ}C$	--	75	--	μV
Ripple Rejection Ratio	RR	$f = 120Hz$, $-15V \leq V_{in} \leq -25V$	55	70	--	dB
Voltage Drop	V_{drop}	$I_{out} = 1.0A$, $T_j = 25^{\circ}C$	--	2	--	V
Output Short Circuit Current	I_{os}	$T_j = 25^{\circ}C$	--	350	--	mA
Peak Output Current	$I_{o peak}$	$T_j = 25^{\circ}C$	--	2.1	--	A
Temperature Coefficient of Output Voltage	$\Delta V_{out} / \Delta T_j$	$I_{out} = 10mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$	--	-1	--	mV/ $^{\circ}C$

TS7915A Electrical Characteristics

($V_{in} = -23V$, $I_{out} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Output voltage	V_{out}	$T_j = 25^{\circ}C$	-14.70	-15	-15.30	V
		$-17.5V \leq V_{in} \leq -30V$, $10mA \leq I_{out} \leq 1A$, $PD \leq 15W$	-14.40	-15	-15.60	
Line Regulation	REG _{line}	$T_j = 25^{\circ}C$				mV
		$-17.5V \leq V_{in} \leq -30V$	--	12	300	
		$-18V \leq V_{in} \leq -22V$	--	3	150	
		$10mA \leq I_{out} \leq 1A$	--	12	300	
Load Regulation	REG _{load}	$T_j = 25^{\circ}C$				mV
		$250mA \leq I_{out} \leq 750mA$	--	4	150	
Quiescent Current	I_q	$T_j = 25^{\circ}C$, $I_{out} = 0$	--	4.3	8	mA
Quiescent Current Change	ΔI_q	$-17.5V \leq V_{in} \leq -30V$	--	--	1	
		$10mA \leq I_{out} \leq 1A$	--	--	0.5	
Output Noise Voltage	V_n	$10Hz \leq f \leq 100KHz$, $T_j = 25^{\circ}C$	--	90	--	μV
Ripple Rejection Ratio	RR	$f = 120Hz$, $-18V \leq V_{in} \leq -28V$	54	69	--	dB
Voltage Drop	V_{drop}	$I_{out} = 1.0A$, $T_j = 25^{\circ}C$	--	2	--	V
Output Short Circuit Current	I_{os}	$T_j = 25^{\circ}C$	--	230	--	mA
Peak Output Current	$I_{o peak}$	$T_j = 25^{\circ}C$	--	2.1	--	A
Temperature Coefficient of Output Voltage	$\Delta V_{out} / \Delta T_j$	$I_{out} = 10mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$	--	-1	--	mV/ $^{\circ}C$

- Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible, and thermal effects must be taken into account separately.
- This specification applies only for DC power dissipation permitted by absolute maximum ratings.

TS7900A Series

3-Terminal Fixed Negative Voltage Regulator

TS7918A Electrical Characteristics

$V_{in} = -24V$, $I_{out} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Output voltage	V_{out}	$T_j = 25^{\circ}C$	-17.64	-18	-18.36	V
		$-21V \leq V_{in} \leq -33V$, $10mA \leq I_{out} \leq 1A$, $PD \leq 15W$	-17.28	-18	-18.72	
Line Regulation	REG _{line}	$T_j = 25^{\circ}C$	--	15	360	mV
		$-21V \leq V_{in} \leq -33V$	--	5	180	
Load Regulation	REG _{load}	$T_j = 25^{\circ}C$	--	12	360	
		$250mA \leq I_{out} \leq 750mA$	--	4	180	
Quiescent Current	I_q	$I_{out} = 0$, $T_j = 25^{\circ}C$	--	4.5	8	mA
Quiescent Current Change	ΔI_q	$-21V \leq V_{in} \leq -33V$	--	--	1	
		$10mA \leq I_{out} \leq 1A$	--	--	0.5	
Output Noise Voltage	V_n	$10Hz \leq f \leq 100KHz$, $T_j = 25^{\circ}C$	--	110	--	μV
Ripple Rejection Ratio	RR	$f = 120Hz$, $-21V \leq V_{in} \leq -31V$	53	68	--	dB
Voltage Drop	V_{drop}	$I_{out} = 1.0A$, $T_j = 25^{\circ}C$	--	2	--	V
Output Short Circuit Current	I_{os}	$T_j = 25^{\circ}C$	--	200	--	mA
Peak Output Current	$I_{o peak}$	$T_j = 25^{\circ}C$	--	2.1	--	A
Temperature Coefficient of Output Voltage	$\Delta V_{out} / \Delta T_j$	$I_{out} = 10mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$	--	-1	--	mV/ $^{\circ}C$

TS7924A Electrical Characteristics

$V_{in} = -33V$, $I_{out} = 500mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$, $C_{in} = 0.33\mu F$, $C_{out} = 0.1\mu F$; unless otherwise specified.)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Output voltage	V_{out}	$T_j = 25^{\circ}C$	-23.52	-24	-24.48	V
		$-27V \leq V_{in} \leq -38V$, $10mA \leq I_{out} \leq 1A$, $PD \leq 15W$	-23.07	-24	-25.96	
Line Regulation	REG _{line}	$T_j = 25^{\circ}C$	--	18	480	mV
		$-27V \leq V_{in} \leq -38V$	--	6	240	
Load Regulation	REG _{load}	$T_j = 25^{\circ}C$	--	12	480	
		$250mA \leq I_{out} \leq 750mA$	--	4	240	
Quiescent Current	I_q	$I_{out} = 0$, $T_j = 25^{\circ}C$	--	4.6	8	mA
Quiescent Current Change	ΔI_q	$-27V \leq V_{in} \leq -38V$	--	--	1	
		$10mA \leq I_{out} \leq 1A$	--	--	0.5	
Output Noise Voltage	V_n	$10Hz \leq f \leq 100KHz$, $T_j = 25^{\circ}C$	--	170	--	μV
Ripple Rejection Ratio	RR	$f = 120Hz$, $-27V \leq V_{in} \leq -37V$	50	65	--	dB
Voltage Drop	V_{drop}	$I_{out} = 1.0A$, $T_j = 25^{\circ}C$	--	2	--	V
Output Short Circuit Current	I_{os}	$T_j = 25^{\circ}C$	--	150	--	mA
Peak Output Current	$I_{o peak}$	$T_j = 25^{\circ}C$	--	2.1	--	A
Temperature Coefficient of Output Voltage	$\Delta V_{out} / \Delta T_j$	$I_{out} = 10mA$, $0^{\circ}C \leq T_j \leq 125^{\circ}C$	--	-1	--	mV/ $^{\circ}C$

- Pulse testing techniques are used to maintain the junction temperature as close to the ambient temperature as possible, and thermal effects must be taken into account separately.
- This specification applies only for DC power dissipation permitted by absolute maximum ratings.

TS7900A Series

3-Terminal Fixed Negative Voltage Regulator

Electrical Characteristics Curve




Figure 1. Worst Case Power Dissipation as a Function of Ambient Temperature




Figure 2. Peak Output Current as a Function of Input-Output Differential Voltage




Figure 3. Ripple Rejection as a Function of Frequency




Figure 4. Ripple Rejection as a Function of Output Voltage




Figure 5. Output Voltage as a Function of Junction Temperature




Figure 5. Output Voltage as a Function of Junction Temperature

Application Information





Figure 7. D²PAK Thermal Resistance and Maximum Power Dissipation vs. P.C.B Copper Length

TS7900A Series


3-Terminal Fixed Negative Voltage Regulator

TO-220 Mechanical Drawing



TO-220 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	10.000	10.500	0.394	0.413
B	3.740	3.910	0.147	0.154
C	2.440	2.940	0.096	0.116
D	-	6.350	-	0.250
E	0.381	1.106	0.015	0.040
F	2.345	2.715	0.092	0.058
G	4.690	5.430	0.092	0.107
H	12.700	14.732	0.500	0.581
I	8.382	9.017	0.330	0.355
J	14.224	16.510	0.560	0.650
K	3.556	4.826	0.140	0.190
L	0.508	1.397	0.020	0.055
M	27.700	29.620	1.060	1.230
N	2.032	2.921	0.080	0.115
O	0.255	0.610	0.010	0.024
P	5.842	6.858	0.230	0.270

Marking Diagram




- XX** = Output Voltage
(05=-5V, 06=-6V, 08=-8V, 09=-9V, 12=-12V, 15=-15V, 18=-18V, 24=-24V)
- Y** = Year Code
- M** = Month Code
(A=Jan, B=Feb, C=Mar, D=Apr, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)
- L** = Lot Code
- CZ** = Package Code for TO-220

TS7900A Series


3-Terminal Fixed Negative Voltage Regulator

ITO-220 Mechanical Drawing



ITO-220 DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	9.96	10.36	0.392	0.407
B	6.20 (typ.)		0.244 (typ.)	
C	2.20 (typ.)		0.087 (typ.)	
D	§ 1.40 (typ.)		§ 0.055 (typ.)	
E	15.07	16.07	0.593	0.632
F	0.80 (typ.)		0.031 (typ.)	
G	2.44	2.64	0.096	0.104
H	13.08	13.48	0.514	0.530
I	1.47 (max.)		0.057 (max.)	
J	3.20	3.40	0.125	0.133
K	4.60	4.80	0.181	0.188
L	1.15 (typ.)		0.045 (typ.)	
M	2.44	2.64	0.096	0.104
N	2.60	2.80	0.102	0.110
O	6.55	6.65	0.258	0.262

Marking Diagram




- XX** = Output Voltage
(05=-5V, 06=-6V, 08=-8V, 09=-9V, 12=-12V, 15=-15V, 18=-18V, 24=-24V)
- Y** = Year Code
- M** = Month Code
(A=Jan, B=Feb, C=Mar, D=Apl, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)
- L** = Lot Code
- CI** = Package Code for ITO-220

TS7900A Series

3-Terminal Fixed Negative Voltage Regulator

TO-263 Mechanical Drawing



DIM	TO-263 DIMENSION			
	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	10.000	10.500	0.394	0.413
B	14.605	15.875	0.575	0.625
C	0.508	0.991	0.020	0.039
D	2.420	2.660	0.095	0.105
E	4.064	4.830	0.160	0.190
F	1.118	1.400	0.045	0.055
G	0.450	0.730	0.018	0.029
H	8.280	8.800	0.325	0.346
I	1.140	1.400	0.044	0.055
J	1.480	1.520	0.058	0.060

Marking Diagram



- XX** = Output Voltage
(05=-5V, 06=-6V, 08=-8V, 09=-9V, 12=-12V, 15=-15V, 18=-18V, 24=-24V)
- Y** = Year Code
- M** = Month Code
(A=Jan, B=Feb, C=Mar, D=Apl, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)
- L** = Lot Code
- CM** = Package Code for TO-263

TS7900A Series

3-Terminal Fixed Negative Voltage Regulator

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.