FCB-405-0624M ✔ ACTIVE

CII | CII FCB-405 Series

TE Internal #: 8-1617760-5

General Purpose Power Relay, DC, Polarized, Monostable, 4 Form C 4PDT-CO, 5 A Contact Rating, 28 VDC Coil Voltage, Panel Mount, CII FCB-405 Series

View on TE.com >

Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Power Relay**

Coil Magnetic System: **Polarized, Monostable**

Contact Arrangement: **4 Form C 4PDT-CO**

Current Type: **DC**

Contact Current Rating: **5 A**

Features

Product Type Features

Relay & Contactor Type	General Purpose Power Relay

Configuration Features

Coil Special Features	Coil Suppression Diode
Relay Options	Back EMF Suppression
Contact Arrangement	4 Form C 4PDT-CO

Electrical Characteristics

Coil Resistance	400 Ω
Contact Current Rating	5 A
Coil Voltage Rating	28 VDC

Body Features

Enclosure Type	Hermetically Sealed

Contact Features

Contact Material	Silver Cadmium Oxide
Terminal Plating	Tin-Lead

Termination Features

Main Termination & Connection Type	Solder Hook Terminals
Coil Termination & Connection Type	Solder Hook Terminals

Downloaded from Arrow.com.

Mechanical Attachment

Product Mounting Feature Type	Mounting Brackets
Product Mount Type	Panel Mount

Usage Conditions

Operating Temperature Range	-70 – 125 °C[-94 – 257 °F]
Environmental Ambient Temperature (Max)	125 °C[257 °F]

Operation/Application

Vibration Resistance	20G's, 70 – 3000Hz
Shock Resistance	100G's, 6ms
Coil Magnetic System	Polarized, Monostable
Current Type	DC

Other

Contact Current Class	>2 – ≤5 A

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

Downloaded from Arrow.com.


on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 4-1617758-7
FCB-205-0222M=M83536/2-022M

Also in the Series | CII FCB-405 Series



General Purpose Power Relays(22)



PCB Relays(10)




Plug-In Relays(6)


Customers Also Bought



TE Part #YD369-P99-NS300000
369 9 WAY PLUG, 20/22 CONTACTS, SKT




TE Part #331243-000
55A0822-16-9/96CS2275




TE Part #485403-000
SO96-4-00




TE Part #YD369-R66-NS300000
369 6 WAY REC, 20/22 CONTACTS, SKT




TE Part #2-1617754-3
FCA-410-1624M=M83536/16-024M



TE Part #4-1617758-0
FCB-205-0208M=M83536/2-008M



TE Part #7-1617760-0
FCB-405-0524M=M83536/5-024M



TE Part #8-1617760-1
FCB-405-0621M=M83536/6-021M

Downloaded from Arrow.com.

TE Part #5-1617791-1
FCA-125-3702L=M83536/37-002L



TE Part #ES405E5M1374
ES405E5M1374=RELAY

Documents

Product Drawings

FCB-405-0624M=M83536/6-024M

English

Datasheets & Catalog Pages

5-1773450-5_sec5_FCB-405

English

relays_brochure

English

Downloaded from Arrow.com.