

Heavy-Duty PDU Power Cable, C13 to C14 - 15A, 250V, 14 AWG, Green, 6 ft. (1.83 m)

MODEL NUMBER: P005-006-GN



Computer power cord extends your existing C13-to-C14 power connection as much as 6 feet.

Features

Power Cable for Network Devices That Require a Heavy-Gauge Connection This 14 AWG C14-to-C13 computer power cord is appropriate for high power connections and a dependable solution for server applications that demand a higher-rated, heavier-gauge cable. You can use this computer power cable for connecting a server, hard drive, monitor or computer to a PDU or UPS system. It's a worthy upgrade or replacement for the power cable that came included with your device. At 6-ft. (1.83 m), the P005-006-GN gives you some flexibility in placing your connected devices.

Green Connectors for Fast, Easy ID That Can Save Costly Downtime This 6-ft. (1.83 m) computer power cable features fully molded green C14 and C13 connectors. This allows you to color-code your connection in a crowded workstation or rack, helping you quickly identify it and prevent an accidental disconnection.

Highlights

- Ideal for powering your server, computer or other network component
- PDU power cable upgrades or replaces the manufacturer's standard computer power cord
- 14 AWG construction designed to handle high power levels needed for powering large equipment
- Green connectors allow quick identification in a crowded workstation or rack
- 6-ft. (1.83 m) power cable gives you flexibility in placing your devices away from an outlet

Applications

- Connect a computer, server, hard drive or display to a PDU or UPS up to 6-ft. (1.83 m) away
- Replace or update the standard power cable provided by your device's original manufacturer
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack

Package Includes

- P005-006-GN Heavy-Duty Power Cable, Green, 6-ft. (1.83 m)

Specifications

OVERVIEW	
UPC Code	037332168368
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Plug Color	Green
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.20mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.71
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Storage Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Operating Humidity Range	20-80% RH
Storage Humidity Range	20-80% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
High Voltage	Yes
Locking Plug	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/Cul, RoHS, REACH
Approvals	UL /CSA
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>