

3W Convection cooled

AC-DC power supplies 

The VCE03 is a series of open frame (suffix -P) and encapsulated AC-DC single output power supplies designed for low cost ITE and industrial electronics applications. Their compact design features an integral EMC filter and hold-up capacitor, so no external components are required.


The series provides two mechanical options including open frame and encapsulated SIL PCB mount. With approvals to world-wide safety standards, compliance with class B for conducted and radiated emissions and a 130%, 30s peak load capability, these class II isolation parts benefit system designers with easy integration into a wide range of applications.



Features

- ▶ Regulated single outputs 3.3 to 48VDC
- ▶ Wide input range 85 to 305VAC
- ▶ PCB mount SIL package
- ▶ Encapsulated & open frame versions
- ▶ ITE & household appliance approvals
- ▶ Class II operation
- ▶ No load input power <0.3W
- ▶ -25°C to +70°C operating temperature
- ▶ 3 year warranty

Applications



Dimensions

VCE03:
40.6 x 19.1 x 19.1mm (1.60" x 0.75" x 0.75")

VCE03-P:
38.1 x 16.5 x 16.5mm (1.50" x 0.65" x 0.65")

Documentation

For further information click the link or scan the code

→ xppower.com



Models & ratings

Model number ¹⁾	Output voltage	Output current	Output power
VCE03US03	3.3VDC	910mA	3W
VCE03US05	5.0VDC	600mA	3W
VCE03US09	9.0VDC	333mA	3W
VCE03US12	12.0VDC	250mA	3W
VCE03US15	15.0VDC	200mA	3W
VCE03US24	24.0VDC	125mA	3W
VCE03US48	48.0VDC	63mA	3W

Notes:

1. For Open Frame version add suffix -P to model number, e.g. VCE03US12-P.



Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Input voltage range	85		305	VAC	Covers all standard voltages in range from 100VAC to 277VAC
Input frequency	47		63	Hz	
Input current - full load		0.10/0.06/0.04		A rms	At 115/230/277VAC
No load input power			0.3	W	
Inrush current			40/44.2	A	At 230/277VAC, cold start +25°C
Earth leakage current	Class II construction no earth				
Input protection	External T1.0 A/300 VAC fuse required in line				

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Output voltage	3.3		48	VDC	
Initial set accuracy			2/1	%	At 50% load for 3.3 & 5V models/Other models
Minimum load	0			A	No minimum load required
Total regulation			5/3	%	For 3.3 & 5V models/other models: from 10% to 100% load. Includes initial set accuracy, line and load regulation. Total regulation is 7% max from 0% to 100% load.
Start up delay			2	s	
Start up rise time			30	ms	
Hold up time	16	20		ms	At full load and 115VAC
Transient response			4	%	Deviation, recovery within 1% in less than 500µs for a 25% load change
Ripple & noise			180/120	mV pk-pk	3.3 & 5V/9V models, 20MHz bandwidth
			1	% pk-pk	12V to 48V models, 20MHz bandwidth
Overvoltage protection	115		140	% Vnom	210% typical for 3.3V models, auto recovery
Overload protection	130		170	%	
Short circuit protection					Trip & Restart (hiccup mode)
Temperature coefficient			0.02	%/°C	

General


Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Efficiency		80		%	At 115VAC, model dependent, see efficiency graphs
Isolation: Input to Output	3000			VAC	
Switching Frequency	5		52	kHz	Varies with load
Power Density			0.286 (4.7)	W/cm³ (W/in³)	For '-P' version
Mean Time Between Failure	400			khls	MIL-HDBK-217F, +25°C GB
Weight		11 (0.025)		g (lb)	Open frame versions (-P)
		30 (0.067)			Encapsulated version

Environmental


Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Operating temperature	-25		+70	°C	Derate linearly from 100% at +50°C to 50% at +70°C
Storage temperature	-40		+85	°C	
Cooling	Convection-cooled				
Humidity			95	%RH	Non-condensing
Operating altitude			5000	m	
Shock	IEC68-2-27, 30 g, 11 ms half sine, 3 times in each of 6 axes				
Vibration	IEC68-2-6, 2 g, 10Hz to 500kHz, 10 mins/cycle, 60 mins each cycle				

Efficiency graphs

VCE03US12-P



VCE03US24-P



EMC: emissions

Phenomenon	Standard	Test Level	Notes & conditions
Conducted	EN55032	Class B	If output is connected to a ground additional external components will be required. See application notes
Radiated	EN55032	Class B	
Harmonic currents	EN61000-3-2	Class A	
Voltage flicker	EN61000-3-3		



EMC: immunity

Phenomenon	Standard	Test Level	Criteria	Notes & conditions
ESD immunity	EN61000-4-2	$\pm 6\text{kV}$ contact, $\pm 8\text{kV}$ air discharge	A	
Radiated immunity	EN61000-4-3	10 V/m	A	
EFT/burst	EN61000-4-4	3	A	
Surge	EN61000-4-5	2	A	Line to Line
Conducted	EN61000-4-6	10 Vrms	A	
Magnetic fields	EN61000-4-8	30A/m	A	
Dips and interruptions	EN61000-4-11 (115 VAC)	70% U_T (80.5 VAC) for 100ms	A	
		40% U_T (46 VAC) for 200ms	B	
		<5% U_T (0 VAC) for 10ms	A	A at High Line, B at Low Line
		<5% U_T (0 VAC) for 5000ms	B	
	EN61000-4-11 (230 VAC)	70% U_T (161 VAC) for 100ms	A	
		40% U_T (92 VAC) for 200ms	A	
		<5% U_T (0 VAC) for 10ms	A	A at High Line, B at Low Line
		<5% U_T (0 VAC) for 5000ms	B	


Safety approvals

Certification	Standard	Notes & conditions
CB	IEC60950-1	ITE
	IEC62368-1	
	IEC60335-1	Household, encapsulated version
	IEC61558-1	Power supply units
UL	UL62368-1	ITE
TUV	EN62368-1	ITE
CE	Meets all applicable directives	
UKCA	Meets all applicable legislation	

Application notes

EMC with output grounded

This product is designed for class II operation, but if there is a requirement to connect the output to ground then the external filter components shown in the diagram can be added to improve emissions.





Suggested component values -
L: 20mH, 500mA common mode choke such as Würth Elektronik 744821120. C: X2 capacitor, 0.1 μ F, 275VAC





Mechanical details

Encapsulated



Pin connections	
Pin	Single
1	ACL
2	ACN
3	+Vout
4	-Vout

Open Frame (-P)



Notes:

- Dimensions in mm (inches).
- Weight: Open frame versions (-P): 10g (0.025 lbs)
Encapsulated: 30g (0.067 lbs)

- Tolerances: x.x (x.xx) = ± 0.5 (± 0.02) x.xx (x.xxx) = ± 0.25 (± 0.01)