



CIO-777-PR

Communication link to PLC/SCADA/
monitoring systems



Wiring Diagram



Specifications

Input Characteristics

Power Requirements

Voltage (nominal)

12-24VDC

Current

150mA (max.)

Power

3.6 W (max.)

Digital Inputs

Voltage Range

12-24VAC

Maximum Current

2mA (typical)

Remote Reset

24VDC, 10mA, (min.), NO pushbutton

Output Characteristics

Form A & Form C Contactors

Pilot Duty

480VA @ 240VAC, B300

General Purpose

5A @ 240VAC

General Characteristics

Ambient Temperature Range

-20° to 70°C (-4° to 158°F)

Operating

-40° to 80°C (-40° to 176°F)

Storage

10-95%, non-condensing per IEC 68-2-3

Relative Humidity

Solid or stranded, 12-20 AWG

Wire Gauge

3 in.-lbs.

Terminal Torque

Hi-Potential Test

(relays to other circuits)

Meets UL508 (2 x rated V + 1000V for 1 min.)

Description

The CIO-777-PR Module is a convenient and cost-effective Profibus interface capable of providing discrete control and monitoring of motor starters, drives and other devices over a Profibus network.

Features & Benefits

FEATURES	BENEFITS
Compact size 3.4" H x 1.0" W x 5.46" D	Easily adapts to existing as well as new applications
Flexible addressing standard allows function as stand-alone interface or in conjunction with 777 series overload relay	Provides flexibility for control and monitoring
Remote reset option	Additional remote reset input allows user to reset 777 series relays without opening the panel
DIN rail or surface mountable	Allows installation flexibility
Built in sub-D connector	Provides a quick and easy connection to a network and reduces field wiring

EMC Standards

Electrostatic Discharge (ESD) IEC 61000-4-2, Level 3, 6kV contact, 8kV air

Radio Frequency

Immunity, Radiated 150 MHz, 10V/m

Fast Transient Burst IEC 61000-4-4, Level 3, 4kV input power

Safety Marks

UL508 (File #E68520)

UL, ULC Listed C22.2 (File #46510)

CSA Polycarbonate

Enclosure

Dimensions H 86.36 mm (3.4"); W 25.4 mm (1.0");

D 138.68 mm (5.46") (w/depluggable connectors)

Weight 0.25 lb. (4 oz., 113.4 g) (w/depluggable connectors)

Mounting Methods DIN Rail or surface mount (w/ two #8 screws)