Booth # 1380

Product Navigation	Home	About Us	Products	Investor Relations	News	Contact Us	Secure EA	×Χ

Circuit Board Indicators					
Panel Mount Indicators	Circuit Board Indicators - Through Hole Indicators				
e bleu i i li	P/N# 5530212002F	3 mm Lens			
Solid State Lighting					
Traffic Signals	Description Package Options	3 mm Bi-Level CBI 60 Pieces Per Tube			
Vehicle Lighting	Product Type	Through Hole Indicators with Bi-Level Housing 3 mm Lens			
Rail	Sub Product Type Configuration				
Obstruction Lighting	Viewing Viewing Angle	Right Angle			
Hazardous Area Lighting	Test Current (mA)	2mA			

Heliport Lighting Absolute Maximum Ratings how to purchase Solder Temp 260° for 5 sec sales contacts Operating Temp -55 to +100° C - stock check Storage Temp -55 to +100° C

Distributor Stock Check

Check stock with our distributors now.

5530212002F

check stock 🕻



Q search Product Line Search Please select a Product Line to search. Circuit Board Indicators 💌 find () Part # / Text Search Part No.: Text Search:

search 🔪 → quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs": by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. View PDF File

Application Notes FAQs

Dialight Ltd (UK) Dialight Garufo Dialight BLP LumiDrives

Operating Characteristics						
LED Position	Found in position(s): 1	Found in position(s): 2				
Color	Red	Green				
Lamp Type	Single Color	Single Color				
LED Type	Low Current	Low Current				
Intensity Min (mcd)	1.0	1.0				
Intensity Typ (mcd)	1.6	1.6				
Intensity Max (mcd)						
Fwd Voltage Min						
Fwd Voltage Typ						
Fwd Voltage Max						
Dom Wavelength Min (nm)						
Dom Wavelength Typ (nm)						
Dom Wavelength Max (nm)						
Power Dissipation Max (mW)	20	20				
Backlighting						
Pitch Between Vertical						
Pitch Between Horizontal						
Lum Intensity Min						
Lum Intensity Typ						
Long Today old and						



Lum Intensity Max