




Technical Data

12.04.2021

Heat shrinkable tubing adhesive lined
EPS-400 - 4:1 shrink ratio

EPS-400-32/8

Article Number 341-32080



Material: Polyolefin, chemically cross-linked (PO-X)
Colour: Black (BK)
Adhesive: Hot melt adhesive

Supplied \emptyset D min.: 32.0 mm
Recov. \emptyset d max.: 8.0 mm
Wall (WT): 2.50 mm
Shrink Ratio: 4:1
Longitudinal Change After Shrinkage: -5 % max.
Min. Shrink Temperature - °C: +120 °C

Test Method

Flammability: ASTM D2671 (outer layer only)
Operating Temperature - °C: -55 °C to +125 °C
Heat Shock Test: 4h/200°C
Tensile Strength at Heat Shock: 12 MPa
Behaviour At Low Temperature: not cracking

IEC 60684-2

Dielectric Strength: 45 kV/mm
Tensile Strength: 14 MPa
Elongation at break: 450%
Specifications: SAE - AMS - DTL-23053/4

IEC 6084-2

IEC 6084-2

IEC 6084-2



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved