

1393817-7 Product Details



1393817-7

(V23003A 37B104)

TE Part Number: 1393817-7

Active

Add to Part List

Communications/Signal PC Board Relays

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- V23003/Cradle Relay P Series
- DC Actuating System
- Input Voltage = 24 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 2 Amps.

View all Features | Find Similar Products

Quick Links

Check Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Request Samples

NEW!

Documentation & Additional Information	
Product Drawings: None Available Catalog Pages/Data Sheets: None Available Product Specifications: Cradle P Relay Datasheet (PDF, English) Application Specifications: None Available Instruction Sheets: None Available CAD Files: None Available	Additional Information: Product Line Information Related Products: Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: Termination Type = Solder/Plug-In Terminals Electrical Characteristics: Actuating System = DC Input Voltage (VDC) = 24 Contact Current Rating (Amps.) = 2 Coil Resistance (Ω) = 340, 400 Coil Power, Nominal (mW) = 1650 Dielectric Between Coil and Contacts (V rms) = 500 Body Related Features: Series = V23003/Cradle Relay P Polarized = Yes Contact Related Features: Number of Bistable Coils = Double Mounting Options = Socket Enclosure = Dust Protected FCC Part 68 Isolation = No Approved Standards = None Contact Material = Silver, Gold Overlay Approx. Dimensions (L x W x H) (mm [in]) = 24.00 x 19.00 x 30.00 [.945 x .748 x 1.181] Compatible Socket = With Contact Type = Single Pin Configuration = Industry Standard	Configuration Related Features: Contact Arrangement = 2 Form C, DPDT, 2 C/O Coil Magnetic System = Polarized, Bistable Coil Suppression Diode = Without Industry Standards: RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C RoHS/ELV Compliance History = Converted to comply with RoHS directive Other: Brand = Axicom