

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RW8405-A2

M BZ-2RW8405-A2

PAGE 1 OF 1

DRAWING
NUMBER

5

ISSUE

REPLACES X72350-BZ

RELEASE NO. PR-10186

CHECK

CHECK

16 MAY 81

CEB

81 CHECK

14 MAY

G J W


REVISIONS
A C063950
J A S
1 NOV 88

B C073287-C
K D R
21 JUN 93

C C076598
K D R
3 SEP 93

D C093346
D L T
14 SEP 98

FORMTEK
FO-52848-A
DRAWN




NOTE

⚠ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ----- 1 OZ MAX

RELEASE FORCE ----- 1/8 OZ MIN

DIFFERENTIAL TRAVEL ----- .007 - .050

OVERTRAVEL ----- .219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

UL LISTED-FILE E12252
CODE L96 15A-125, 250 OR 480 VAC
1/8 HP-125 VAC; 1/4 HP-250 VAC
1/2 A-125 VDC; 1/4 A-250 VDC

L288
L299
L306



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.01/0.25
ONE PLACE	X.X	0.4/.016	X.X	0.004/.10
TWO PLACES	X.XX	0.16/.006	X.XX	0.001/.025
THREE PLACES	X.XXX		X.XXX	

DESIGN UNITS ☐ SI METRIC ☐ US CUSTOMARY

WEIGHT .073 LB.