

Power Matters.™

Home ▶ 2N4000 (#23184)

Products

- ▶ Product Directory
- ▶ Applications Directory
- ▶ Parametric Search

2N4000 (#23184)

Overview

Diagrams

Electrical Rating	Symbol	Min	Typ	Max	Unit
Collector to Emitter Saturation Voltage	V _{CE(sat)}			0.50	V
DC Current Gain	HFE	30.00		120.00	

Maximum Electrical Rating	Symbol	Min	Typ	Max	Unit
Breakdown Voltage, Collector-Base (Emitter Open)	V _{BR(CBO)}			100.00	V
Collector Current (dc)	I _C			1.00	A
Collector-Emitter Voltage (Base Open)	V _{CEO}			80.00	V
Emitter-Base Voltage (Collector Open)	V _{EBO}			8.00	V
Power Dissipation, Total	P _T			1.00	W

This part can be found in the following product categories:

- ▶ Discretes ▶ Transistors ▶ BJT(BiPolar Junction Transistor) ▶ PNP Transistor
- ▶ Non-Radiation Hardened Devices ▶ Transistors ▶ BJT(BiPolar Junction Transistor) ▶ NPN Transistor

Related Links

- Technical support
- Sales Contacts
- Available Stock
- Sales Contacts
- RFQ/Samples