





REVISIONS			
REV	DESCRIPTION, E.C.N., E.A.R. NO.	DATE	APP'D
A	INITIAL DRAWING	SEP11/25	E.Q.
B	ADD PLATING OPTION	NOV05/25	E.Q.

1



RECOMMENDED WALL OPENING

3

SCREW
2- 4-40UNC-2A
X 1/4" LONG

PANEL FLANGE

COUPLER

NOTES:

1. MATERIALS:
PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0, BLACK.

CONTACTS: PHOSPHOR BRONZE
PLATING: GOLD ON MATING SURFACES
(SEE PART NO. FOR THICKNESS).
50µ" (1.27 MICRONS)
MIN. NICKEL UNDERPLATE

SHIELD: STAINLESS STEEL

PANEL FLANGE : DIECAST ZINC ALLOY.

2. THE PART IS CONFORMED TO TIA-1096

3. PACKAGING : PE BEG, A BEG CONTAIN A COUPLER,
A PANEL FLANGE AND 2 SCREWS.

PART NUMBER: RJE17-288-7X13-P

GOLD PLATING
1 = 0.15µm (6µ")
2 = 0.38µm (15µ")
3 = 0.76µm (30µ")
4 = 1.27µm (50µ")

PANEL FLANGE & COUPLER & SCREWS
PACK IN PE BAG WITH UN-ASSEMBLY STATUS



UNLESS SPECIFIED OTHERWISE	DRAWN	W.QIU	SEP11/25
PRIMARY UNITS	MILLIMETERS	CHECKED	E.QU
SECONDARY		M.E. APP'D	
REFERENCE IN PARENTHESES		Q.A. APP'D	
GENERAL TOLERANCES		DWG APPR.	
1 DECIMAL PLACE	±0.50	ENG. REL. NO.	
2 DECIMAL PLACES	±0.38	REF.	EAR 16302
3 DECIMAL PLACES	±0.25	THIRD ANGLE PROJECTION	
ANGULAR DEGREES	±1.0°	DO NOT SCALE DRAWING	

Amphenol Canada Corp.			
Commercial Products			
CAT 5E COUPLER JACK, RJ45, 8P8C, SHIELD, WITH PANEL FLANGE AND SCREW, PE BAG PACKAGING, -RoHS COMPLIANT			
DWG. NO.	P-RJE17-288-7X13-P		
CODE ID NO.	03554	DWG SIZE:	X
SCALE:	4:1	SHEET	1 OF 1
REV	B		