

Han 16HPR EasyCon cover 4XM25 for Female



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 19 40 016 9902 |
| Specification | Han 16HPR EasyCon cover 4XM25 for Female |
| HARTING eCatalogue | https://b2b.harting.com/19400169902 |

Identification

| | |
|-----------------------------|---|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] HPR EasyCon |
| Type of hood/housing | Mounting cover |
| Description of hood/housing | for surface mounted housings for hoods |

Version

| | |
|----------------------|--|
| Size | 16 HPR |
| Cable entry | 4x M25 |
| Locking type | Screw locking |
| Field of application | Hoods/housings for harsh outdoor environments |
| Details | Not compatible to cable glands 19 00 000 5013 and 19 00 000 5019 |

Technical characteristics

| | |
|--|---|
| Tightening torque | 6 Nm Mounting cover 6 Nm Distance bolt 6 Nm Fixing screws |
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 IP68 IP69 / IPX9K acc. to ISO 20653 |



Pushing Performance
Since 1945

Technical characteristics

| | |
|------------------------------------|----|
| Type rating acc. to UL 50 / UL 50E | 4 |
| | 4X |
| | 12 |

Material properties

| | |
|--------------------------------------|---|
| Material (hood/housing) | Aluminium die-cast Corrosion resistant |
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (seal) | NBR |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Naphthalene |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R1 (HL 1-3) |
| | R7 (HL 1-3) |

Specifications and approvals

| | |
|-----------|-----------------------------------|
| Approvals | DNV GL |
| UL / CSA | UL 1977 ECBT2.E235076 |
| | CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 199.1 g |
| Country of origin | China |
| European customs tariff number | 85389099 |
| GTIN | 5713140175242 |
| eCl@ss | 27440202 Shell for industrial connectors |