
Part Number : 22162140
Product Description : KK 254 PC Board Connector, Right-Angle, End-to-End Stackable, 0.38µm Gold (Au) Plating, 14 Circuits
Series Number : 4455
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : A-4455-AZ14A(208)



Documents and Resources

Drawings

022162140_sd.pdf

PK-44646-001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PS-10-07-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	4455
Description	KK 254 PC Board Connector, Right-Angle, End-to-End Stackable, 0.38µm Gold (Au) Plating, 14 Circuits
Application	Board-to-Board
Component Type	PCB Receptacle
Product Name	KK 254
UPC	800754240499

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	500V

Physical

Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Natural (White)

Downloaded from Arrow.com.

Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Mounting Style	Through Hole
Net Weight	1.463/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.35mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to PCB	Yes
Stackable	Yes
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 RPC Vertical Headers with Friction Lock	171856
KK 254 RPC Right-Angle Headers with Friction Lock	171857
KK 254 Single Row Vertical Headers	4030
KK 254 Single Row Right-Angle Headers	4094
KK 254 Vertical Breakaway Headers with Friction Lock	42375
KK 254 Right-Angle Breakaway Headers	42376
KK 254 Right-Angle Surface Mount Compatible Breakaway Headers	42377

Downloaded from Arrow.com.