

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks.

MTP/MPO Multimode Patch Cable, 12 Fiber, 40Gb, 40 GBASE-SR4, OM3 Plenum-Rated (M/F), Aqua, 10M (32 ft.)

MODEL NUMBER: **N842-10M-12-MF**



Premium multimode fiber optic cabling for transmitting 40 Gb data and voice signals over short distances. Designed to extend high-density connections between network equipment in telecommunication rooms.

Description

The N842-10M-12-MF MTP/MPO Multimode Patch Cable is a 10-meter patch cable that supports 40 Gb Ethernet speeds and is designed for high-density connections between network equipment in telecommunication rooms and data centers. With one male and one female MTP/MPO connector, this OM3-rated multimode fiber optic cable allows IT professionals to extend the length of their connection and eliminates the need for long fan-out cables or individual long duplex cable runs. MTP / MPO Extension cables used with Tripp Lite High Density patching systems, in particular MTP/MPO Feed-Through Cassettes, such as Tripp Lite N484-12M12.

The 12-fiber MTP/MPO connectors are about the same size as SC connectors, but are 12 times denser, freeing up circuit card and rack space for other cables. The cable has documented insertion loss and back reflection testing on every connector and attenuation loss that meets or exceeds current standards. Push/pull tab connectors are easily accessible in high-density data center applications and make the cable easy to install and remove with one hand.

Backward compatible with existing 50/125 fiber, the aqua-colored N842-10M-12-MF has 50/125 duplex (zipcord) fiber made from glass, as well as a plenum-rated jacket for connecting high-speed network components in ceilings, walls and ducts. The laser-optimized multimode fiber (LOMMF) cable meets the most current industry standards, including IEEE 802.3ae and TIA LOMMF.

Features

OM3-Rated for 40 Gb Ethernet Applications

Highlights

- 40 Gb Ethernet speed up to 300 m (@ 850 nm)
- Push/pull tab connectors install/remove with one hand
- 12-fiber MTP/MPO connector with 12x density of SC connector
- 100% tested for low insertion loss and back reflection
- 50/125 OM3-rated multimode fiber

Package Includes

- N842-10M-12-MF MTP/MPO Multimode Patch Cable (M/F), Aqua, 10 m (32 ft.)



- Designed to extend high-density connections between network equipment in telecommunication rooms
- Provides 3x more bandwidth than conventional 62.5 µm multimode fiber
- Backward compatible with existing 50/125 fiber
- Meets current IEEE 802.3ae and TIA LOMMF standards

MTP/MPO Connectors with Push/Pull Tabs

- 12-fiber male/female connectors 12 times denser than SC connectors
- Push/pull tab connectors easy to install and remove with one hand
- 100% tested for low insertion loss and back reflection

Error-Free Signal Transfer

- 50/125 duplex glass fiber construction
- Plenum-rated jacket perfect for ceilings, walls and ducts
- Aqua-colored for identification as a 10 Gb cable

Specifications

OVERVIEW	
UPC Code	037332191076
Clad Diameter	125 micron
Core Diameter	50 micron
Number of Fibers	12
Optical Mode	OM3
INPUT	
Cable Length (ft.)	32.8
Cable Length (m)	10
Cable Length (in.)	393.7
PHYSICAL	
Color	Aqua
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
COMMUNICATIONS	
Network Speed	10Gbps / 40Gbps / 100Gbps



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Side A - Connector 1	12-STRAND MTP (MALE)
Side B - Connector 1	12-STRAND MTP (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	Multimode; MTP/MPO
SPECIAL FEATURES	
Push/Pull Tabs	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>