



Product: [8443](#) 

Electronic, 3 C #22 Str TC, PVC Ins, PVC Jkt, CMG

 [Request Sample](#)

Product Description

Electronic, 3 Conductor 22AWG (7x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	22	7x30	TC - Tinned Copper	3

Conductor Count:	3
------------------	---

Insulation

Element	Material	Nominal Wall Thickness
Conductor(s)	PVC - Polyvinyl Chloride	0.011 in

Color Chart

Color
Black
Red
Green

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.172 in	0.032 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
15.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
34 pF/ft

Inductance

Nominal Inductance
0.17 μ H/ft

Current

Max. Recommended Current [A]
2.9 Amps per conductor @ 25°C

Voltage

UL Description	UL Voltage Rating
CMG	300 V
UL AWM 2576	150 V

Temperature Range

UL Temp Rating:	80°C (UL AWM 2576)
Operating Temp Range:	-20°C to +80°C

Mechanical Characteristics

Bulk Cable Weight:	16 lbs/1000ft
Max Recommended Pulling Tension:	27 lbs
Min Bend Radius/Minor Axis:	1.75 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	2576
CSA AWM Specification:	FT4
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V (CMG), 150 V UL AWM 2576)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
8443 060100	Chrome	Reel	100 ft	612825207320
8443 060500	Chrome	Reel	500 ft	612825207344
8443 060U500	Chrome	UnReel	500 ft	612825207313
8443 0601000	Chrome	Reel	1,000 ft	612825207337
8443 060U1000	Chrome	UnReel	1,000 ft	612825207306
8443 0605000	Chrome	Reel	5,000 ft	612825207351

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.289 Revision Date: 05-19-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.