


| PRODUCT NUMBER | COLOR | LENGTH |
|--------------------|-------------|--------|
| 10152943-Z0500YBLF | BLACK | 500 |
| 10152943-Z0500YGLF | COOLGREY 9C | |
| 10152943-Z0500YWLF | WHITE | |





ELECTRICAL TEST


1. 100% OPEN, SHORT & INTERMITTANCE TEST
2. INSULATION RESISTANCE: 10MΩ Min.
3. HI-PORT: DC 300V/10ms
4. CONDUCTOR RESISTANCE:

CONDUCTOR RESISTANCE FOR Vbus: 1.5Ω Max
CONDUCTOR RESISTANCE for GND: 1.5Ω Max

5. PRODUCT REFER TO GS-12-1577

| | | | | | | | | | | | | |
|-------------|----------------|---|----------|---------------------------------------|---------|-------------------------------|-------|---|--|--|--|------|
| A/R | KG | Ø 8MM SOLDER WIRE L/F | | | | | | | | | | 6 |
| A/R | KG | OVER MOLDED: BLACK/COOL GREY 9C TPE,WHITE | | | | | | | | | | 5 |
| A/R | KG | INNER MOLDED: PP | | | | | | | | | | 4 |
| 1 | EA | USB TYPE-C PLUG:SHELL Ni PLATING , HOUSING:WHITE, PCB:56KΩ RESISTOR | | | | | | | | | | 3 |
| 1 | EA | USB2.0 A/M: SHORT TYPE, HOUSING:WHITE, SHELL: Ni PLATING SALT SPRAY 24H | | | | | | | | | | 2 |
| A/R | M | NO UL 30AWG*1P +24WG*2C+AL JACKET OD:3.5MM,TPE/COOL GREY 9C ,BLACK ,WHITE | | | | | | | | | | 1 |
| Qty | Unit | Description | | | | | | | | | | Item |
| mat'l. code | | | | surface ISO 1302 | | tolerance ISO 406 ISO 1101 | | projection  | | product family Cable Assembly | | |
| ltr | ecn no | dr | date | tolerances unless otherwise specified | | | |  MM | | title USB Cable Round Type A – Type C | | |
| A | / | St | 1 /7'19 | angles | linear | .000 | ±0.15 | | | | | |
| B | N-36968 | St | 5 /06'20 | | | .00 | ±0.35 | | | | | |
| | | | | ±3" | | .0 | ±0.5 | scale N/A | | dwg no sheet 1 of 3 10152943 A3 | | |
| | | | | dr | St | 5 /06'20 | | | | | | |
| | | | | engr | St | 5 /06'20 | | | | | | |
| | | | | chr | Tim Yao | 5 /06'20 | | | | | | |
| | | | | appd | Tim Yao | 5 /06'20 | | | | type Customer Drawing | | |
| sheet index | revision sheet | B | 3 | | | | | | | | | |

| PRODUCT NUMBER | COLOR | LENGTH/"L" |
|--------------------|-------------|------------|
| 10152943-Z0100YBLF | BLACK | 1000 |
| 10152943-Z0100YGLF | COOLGREY 9C | |
| 10152943-Z0130YWLF | WHITE | |
| 10152943-Z0130YGLF | COOLGREY 9C | 1270 |
| 10152943-Z0130YBLF | BLACK | |
| 10152943-Z0130YWLF | WHITE | |



ELECTRICAL TEST

1. 100% OPEN, SHORT & INTERMITTANCE TEST
2. INSULATION RESISTANCE: 10MΩ Min.
3. HI-PORT: DC 300V/10ms
4. CONDUCTOR RESISTANCE: 1.5Ω Max

| | | | |
|----------------|----------------|--|----------------------------|
| A/R | KG | Ø 8MM SOLDER WIRE L/F | 6 |
| A/R | KG | OVER MOLDED: BLACK/COOL GREY 9C ,WHITE TPE | 5 |
| A/R | KG | INNER MOLDED: LD-PE | 4 |
| 1 | EA | USB TYPE-C PLUG: SHELL Ni PLATING , HOUSING: WHITE, PCB: 56KΩ RESISTOR | 3 |
| 1 | EA | USB2.0 A/M: SHORT TYPE, HOUSING: WHITE, SHELL: Ni PLATING SALT SPRAY 24H | 2 |
| A/R | M | NO UL 30AWG*1P +24WG*2C+AL JACKET OD: 3.5MM, TPE BLACK/COOL GREY 9C, WHITE | 1 |
| Qty | Unit | Description | Item |
| mat'l. code | | surface ISO 1302 ✓ | tolerance ISO 406 ISO 1101 |
| ltr | | ecn no | dr |
| A | | / | St |
| B | | N-36968 | St |
| date | | 1 /7'19 | 5 /06'20 |
| angles | | linear | .000 ±0.15 |
| ±3' | | | .00 ±0.35 |
| | | | .0 ±0.5 |
| dr | | St | 5 /06'20 |
| enr | | St | 5 /06'20 |
| chr | | Tim Yao | 5 /06'20 |
| appd | | Tim Yao | 5 /06'20 |
| sheet index | revision sheet | B 3 | |
| product family | | Cable Assembly | |
| title | | USB Cable Round Type A - Type C | |
| dwg no | | 10152943 | sheet 2 of 3 |
| type | | Customer | Drawing |



1. PACKAGE IS JUST FOR REFERENCE ONLY,CAN BE CUSTOMIZED.



2.500PCS/WATERPROOF BAG+CARTON

[illegible]