




PRODUCT NUMBER	PITCH
YK552xx0x0JOG	11.00 mm



MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT: 300 V, 30 A
 WITHSTAND VOLTAGE: AC 2000 V/Min
 INSULATION RESISTANCE: 1000 M Ω OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 9.5 Lb-In.
 WIRE RANGE: 22-10AWG str/sol
 1) HOUSING: Thermoplastic, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M4
 APPROVAL:

DIMENSION

Dim A	Nx11.0+2.0
Dim B	(N-1)x11.0

N=Number of poles

Poles	Tolerance
2p-4p	±0.30
5p-8p	±0.40
9p-16p	±0.50
17p-23p	±0.60
24p-32p	±0.80

PART NO.: YK 552xx 0 x 0 JOG

No. of poles
 02 2 poles
 03 3 poles
 ...
 32 32 poles

Plated		
Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code		surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified	title TERMINAL BLOCK
				angles 	BARRIER TYPE
				X°±1'	scale
				dr EVAN LU 061614	dwg no YK552xx0x0JOG
				enr EVAN LU 061614	sheet 1 of 1 size A4
				chr HANKE FENG 061614	type CUSTOMER Drawing
				appd SHI JUN 061614	
sheet index	revision sheet	A	1		