



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H3	REVISED PER ECN-22-153872	16MAY2022	RK	MF



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 23-10-87	TE Connectivity Ltd.		
DIMENSIONS: INCHES		CHK T. CLARK 23-10-87			
		APVD T. CLARK 29-10-87	NAME		
		PRODUCT SPEC	HEADER ASSY, MOD II, B/A, DR, .100X.100 C/L, RA, WITH .025 SQ POSTS		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
0 PLC ± -		—	A2	00779	C=103326
1 PLC ± -		—	RESTRICTED TO		
2 PLC ± -		—	—		
3 PLC ± .005		—	—		
4 PLC ± -		—	—		
ANGLES ± -		—	—		
FINISH		WEIGHT	—		
MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK POSTS: COPPER ALLOY		—	—		
SEE TABLE		CUSTOMER DRAWING	—		
		SCALE	4:1	SHEET	1 OF 2
		REV	H3		

4

3

2

1

© -TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1

THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING

2

POINT OF MEASUREMENT FOR PLATING THICKNESS.

3

ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS

4

BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT

5

.000015 GOLD IN THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL

6

.000015 GOLD IN THE CONTACT AREA, .000100-.000200 MATTE TIN ON THE SOLDER TAIL, ALL OVER .000050 NICKEL

7

HIGH TEMPERATURE CONFIGURATION

8

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

9

OBSOLETE

7	7	6	3.984	3.900	39	80	9-103326-0	5	3.984	3.900	39	80	9 4-103326-0
7	7	6	3.884	3.800	38	78	8-103326-9	5 5	3.884	3.800	38	78	8 3-103326-9
7	7	6	3.784	3.700	37	76	8-103326-8	5 5	3.784	3.700	37	76	8 3-103326-8
7	7	6	3.684	3.600	36	74	8-103326-7	5 5	3.684	3.600	36	74	8 3-103326-7
7	7	6	3.584	3.500	35	72	8-103326-6	5 5	3.584	3.500	35	72	8 3-103326-6
7	7	6	3.484	3.400	34	70	8-103326-5	5 5	3.484	3.400	34	70	8 3-103326-5
7	7	6	3.384	3.300	33	68	8-103326-4	5 5	3.384	3.300	33	68	8 3-103326-4
7	7	6	3.284	3.200	32	66	8-103326-3	5 5	3.284	3.200	32	66	8 3-103326-3
7	7	6	3.184	3.100	31	64	8-103326-2	5 5	3.184	3.100	31	64	8 3-103326-2
7	7	6	3.084	3.000	30	62	8-103326-1	5 5	3.084	3.000	30	62	8 3-103326-1
7	7	6	2.984	2.900	29	60	8-103326-0	5 5	2.984	2.900	29	60	8 3-103326-0
7	7	6	2.884	2.800	28	58	7-103326-9	5 5	2.884	2.800	28	58	8 2-103326-9
7	7	6	2.784	2.700	27	56	7-103326-8	5 5	2.784	2.700	27	56	8 2-103326-8
7	7	6	2.684	2.600	26	54	7-103326-7	5 5	2.684	2.600	26	54	8 2-103326-7
7	7	6	2.584	2.500	25	52	7-103326-6	5 5	2.584	2.500	25	52	8 2-103326-6
7	7	6	2.484	2.400	24	50	7-103326-5	5 5	2.484	2.400	24	50	8 2-103326-5
7	7	6	2.384	2.300	23	48	7-103326-4	5 5	2.384	2.300	23	48	8 2-103326-4
7	7	6	2.284	2.200	22	46	7-103326-3	5 5	2.284	2.200	22	46	8 2-103326-3
7	7	6	2.184	2.100	21	44	7-103326-2	5 5	2.184	2.100	21	44	8 2-103326-2
7	7	6	2.084	2.000	20	42	7-103326-1	5 5	2.084	2.000	20	42	8 2-103326-1
7	7	6	1.984	1.900	19	40	7-103326-0	5 5	1.984	1.900	19	40	9 2-103326-0
7	7	6	1.884	1.800	18	38	6-103326-9	5 5	1.884	1.800	18	38	8 1-103326-9
7	7	6	1.784	1.700	17	36	6-103326-8	5 5	1.784	1.700	17	36	8 1-103326-8
7	7	6	1.684	1.600	16	34	6-103326-7	5 5	1.684	1.600	16	34	8 1-103326-7
7	7	6	1.584	1.500	15	32	6-103326-6	5 5	1.584	1.500	15	32	8 1-103326-6
7	7	6	1.484	1.400	14	30	6-103326-5	5 5	1.484	1.400	14	30	8 1-103326-5
7	7	6	1.384	1.300	13	28	6-103326-4	5 5	1.384	1.300	13	28	8 1-103326-4
7	7	6	1.284	1.200	12	26	6-103326-3	5 5	1.284	1.200	12	26	9 1-103326-3
7	7	6	1.184	1.100	11	24	6-103326-2	5 5	1.184	1.100	11	24	8 1-103326-2
7	7	6	1.084	1.000	10	22	6-103326-1	5 5	1.084	1.000	10	22	8 1-103326-1
7	7	6	.984	.900	9	20	6-103326-0	5 5	.984	.900	9	20	8 1-103326-0
7	7	6	.884	.800	8	18	5-103326-9	5 5	.884	.800	8	18	8 1-103326-9
7	7	6	.784	.700	7	16	5-103326-8	5 5	.784	.700	7	16	9 1-103326-8
7	7	6	.684	.600	6	14	5-103326-7	5 5	.684	.600	6	14	9 1-103326-7
7	7	6	.584	.500	5	12	5-103326-6	5 5	.584	.500	5	12	9 1-103326-6
7	7	6	.484	.400	4	10	5-103326-5	5 5	.484	.400	4	10	9 1-103326-5
7	7	6	.384	.300	3	8	5-103326-4	5 5	.384	.300	3	8	8 1-103326-4
7	7	6	.284	.200	2	6	5-103326-3	5 5	.284	.200	2	6	8 1-103326-3
7	7	6	.184	.100	1	4	5-103326-2	5 5	.184	.100	1	4	8 1-103326-2
7	7	6	.084			2	5-103326-1	5 5	.084			2	8 1-103326-1
REMARKS	PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:INCHES

MATERIAL-

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC± -
1 PLC± -
2 PLC± -
3 PLC± -
4 PLC± -
ANGLES± -
FINISHSEE TABLE

DWNH MOLL23-10-87
CHKT. CLARK23-10-87
APVDT. CLARK29-10-87

PRODUCT SPEC-
APPLICATION SPEC-
WEIGHT-

CUSTOMER DRAWING

23-10-87

TE Connectivity Ltd.

NAMEHEADER ASSY, MOD II, BREAKAWAY, DR, .100X.100 C/L, RA, WITH .025 SQ POSTS

SIZEA2CAGE CODE00779DRAWING NOC=103326RESTRICTED TO-

SCALE1:1SHEET2 OF 2REVH3

1471-9 (1/15)

Downloaded from Arrow.com