

Certified Peripherals

Products

Solution

Partnership

Procurement Service

CPU and Memory Finder

Advantech Qualified DIMM

Built To Last- The toughest memory module for extreme application





RadiForce MX242W

EIZO



Rescue

Data Recovery Services

Drop it. Dunk it. Delete it.

We can help get your data back to you.

96FD25-S150-INB2



Enlarge

Main Features

- Form factor – 2.5"
- Power loss protection
- Efficiency across power status
- Performance consistency
- End-to-end data protection
- Increased endurance at 1.0 DWPD
- Low Latency
- INTEL 3D NAND Flash MLC 16nm

Datasheet (PDF)

Get Price

Product Spec

Product	96FD25-S150-INB2
Product Description	Intel SSD DC S3520 150GB,2.5" SATA3, MLC 7mm
Manufacturer	Intel
Capacity	150GB
Form Factor	2.5"
Interface	SATA III
Dimension	70.11 x 100.45 x 7 mm
Weight	0.06 kg
Warranty	5 years
Operating Temperature	0 ~ 70 °C (32 ~ 158°F)
Box Contains	TBA
MTBF	2 million hours
RoHS Status	Yes
EOL	N/A

ADVANTECH Online

Buy Online

Live Chat

1-888-576-9668

Contact Us

Price and Quotation

RMA Service

Technical Support

Worldwide Offices

Global eStore

eStore

Retail Store

Warranty Policy

Popular Links

Advantech TALKs

MyAdvantech Magazine

Worldwide Events

Solution Day

About Advantech

Company Information

Investor Relations

Job Opportunities

Citizenship Programs